

MM-EMLC (EX12)R C1 WH/BK - Fabric label



0803934

<https://www.phoenixcontact.com/us/products/0803934>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Fabric label, Roll, Mixed color, unmarked, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: adhesive, roll length: 6 m, text field height: 10 mm, text field width: 6000 mm

Your advantages

- Enables labels to be stuck over edges and curves
- High-quality and solvent-resistant marking solution for industrial applications that is created by means of thermal transfer printing
- The self-adhesive material in continuous format is particularly suitable for the professional and permanent marking of various components and equipment in control cabinet, controller, and systems manufacturing
- The material is cUL certified
- Thanks to the continuous format, a label of the appropriate length can be created flexibly for the relevant application
- The label material consists of a textile foil with very low restoring forces
- Easy and efficient material cartridge system: Includes both the material to be printed and the corresponding ink ribbon



Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 0803934 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | BG23 |
| Product key | BG241E |
| GTIN | 4055626212142 |
| Weight per piece (including packing) | 56 g |
| Weight per piece (excluding packing) | 51.6 g |
| Customs tariff number | 96121010 |

MM-EMLC (EX12)R C1 WH/BK - Fabric label



0803934

<https://www.phoenixcontact.com/us/products/0803934>

| | |
|-------------------|----|
| Country of origin | CN |
|-------------------|----|

MM-EMLC (EX12)R C1 WH/BK - Fabric label



0803934

<https://www.phoenixcontact.com/us/products/0803934>

Technical data

Product properties

| | |
|--------------|---------------|
| Product type | Device marker |
|--------------|---------------|

Marking

| | |
|---------------------------|------------------|
| Identification technology | Thermal transfer |
|---------------------------|------------------|

Dimensions

| | |
|----------------|---------|
| Length of roll | 6.00 m |
| Height | 12 mm |
| Depth | 0.12 mm |

Text field

| | |
|-------------------|---------|
| Text field width | 6000 mm |
| Text field height | 10 mm |

Material specifications

| | |
|-----------------------|--|
| Foil strength | 130 µm |
| Adhesive strength | 28 µm |
| Adhesive | Acrylic |
| Color | multicolored (RAL -) |
| | white (RAL 9010) |
| | black (RAL 9005) |
| Base element material | PA |
| Components | free from silicone, halogen, and cadmium |

Environmental and real-life conditions

Ambient conditions

| | |
|---|----------------|
| Ambient temperature (operation) | 0 °C ... 80 °C |
| Recommended ambient temperature (storage/transport) | 5 °C |
| Recommended humidity (storage/transport) | 30 % ... 80 % |

Test for substances that would hinder coating with paint or varnish

| | |
|---|----------------------|
| Testing for paint wetting impairment substances (LABS-conformity) | VW PV 3.10.7:2005-02 |
| Result | Test passed |

UV resistance

| | |
|---------------|---------------------------------------|
| Specification | DIN EN ISO 4892-2:2021-11 (following) |
| Result | Test passed |
| Test duration | 96 h |

Wipe resistance of inscriptions

| | |
|---------------|--|
| Specification | DIN EN 61010-1 (VDE 0411-1):2011-07 |
| | DIN EN 62208 (VDE 0660-511):2012-06 (in parts) |

MM-EMLC (EX12)R C1 WH/BK - Fabric label



0803934

<https://www.phoenixcontact.com/us/products/0803934>

| | |
|---|-------------|
| Isopropanol (99%) [67-63-0] | Test passed |
| n-Hexane [CAS No. 110-54-3] | Test passed |
| Water + Petroleum ether [CAS No. 64742-82-1] | Test passed |

Testing in a condensation changing climate in the presence of sulfur dioxide

| | |
|---------------|--------------------------|
| Specification | DIN EN ISO 22479:2022-08 |
| Result | Test passed |
| Procedure | Method B |
| Cycles | 2 |

Salt spray test

| | |
|---------------|---|
| Specification | DIN EN IEC 60068-2-11 (VDE 0468-2-11):2022-10 |
| Result | Test passed |

Mounting

| | |
|---------------|----------|
| Mounting type | adhesive |
|---------------|----------|

MM-EMLC (EX12)R C1 WH/BK - Fabric label



0803934

<https://www.phoenixcontact.com/us/products/0803934>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/0803934>



UL Recognized

Approval ID: MH48542-V2_S6

MM-EMLC (EX12)R C1 WH/BK - Fabric label



0803934

<https://www.phoenixcontact.com/us/products/0803934>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27281103 |
| ECLASS-15.0 | 27281103 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC001288 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39131500 |
|-------------|----------|

MM-EMLC (EX12)R C1 WH/BK - Fabric label



0803934

<https://www.phoenixcontact.com/us/products/0803934>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

EF3.1 Climate Change

| | |
|---------|---------------|
| CO2e kg | 1.099 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com