

MM-EMLF (EX10)R C1 OG/BK - Label, highly flexible



0803955

<https://www.phoenixcontact.com/us/products/0803955>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Label, highly flexible, Roll, Mixed color, unmarked, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: adhesive, roll length: 8 m, text field height: 8 mm, text field width: 8000 mm

Your advantages

- High-quality and solvent-resistant marking solution for industrial applications that is created by means of thermal transfer printing
- The self-adhesive material in continuous format is particularly suitable for the professional and permanent marking of various components and equipment in control cabinet, controller, and systems manufacturing
- Thanks to the continuous format, a label of the appropriate length can be created flexibly for the relevant application
- Easy and efficient material cartridge system: Includes both the material to be printed and the corresponding ink ribbon

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 0803955 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | BG23 |
| Product key | BG241E |
| GTIN | 4055626212326 |
| Weight per piece (including packing) | 57.9 g |
| Weight per piece (excluding packing) | 57.9 g |
| Customs tariff number | 96121010 |
| Country of origin | CN |

MM-EMLF (EX10)R C1 OG/BK - Label, highly flexible



0803955

<https://www.phoenixcontact.com/us/products/0803955>

Technical data

Product properties

| | |
|------------------|-----------------|
| Product type | Device marker |
| Product property | Highly flexible |

Marking

| | |
|---------------------------|------------------|
| Identification technology | Thermal transfer |
|---------------------------|------------------|

Dimensions

| | |
|----------------|---------|
| Length of roll | 8.00 m |
| Height | 10 mm |
| Depth | 0.07 mm |

Text field

| | |
|-------------------|---------|
| Text field width | 8000 mm |
| Text field height | 8 mm |

Material specifications

| | |
|-----------------------|---|
| Foil strength | 70 µm |
| Adhesive | Acrylic |
| Color | multicolored (RAL -) orange (RAL 2003) black (RAL 9005) |
| Material | Vinyl polymer |
| Base element material | Vinyl polymer |
| Components | Free from silicone and cadmium |

Environmental and real-life conditions

Ambient conditions

| | |
|---|--|
| Ambient temperature (operation) | -20 °C ... 75 °C |
| Recommended ambient temperature (storage/transport) | 20 °C |
| Recommended humidity (storage/transport) | 45 % ... 55 % (Storage in a dry and dark place in the original packaging is recommended) |

Test for substances that would hinder coating with paint or varnish

| | |
|---|-------------------------|
| Testing for paint wetting impairment substances (LABS-conformity) | VDMA 24364-A1-L:2018-05 |
| Result | Test passed |

UV resistance

| | |
|---------------|---------------------------------------|
| Specification | DIN EN ISO 4892-2:2021-11 (following) |
| Result | Test passed |
| Test duration | 96 h |

Wipe resistance of inscriptions

MM-EMLF (EX10)R C1 OG/BK - Label, highly flexible



0803955

<https://www.phoenixcontact.com/us/products/0803955>

| | |
|---|--|
| Specification | DIN EN 61010-1 (VDE 0411-1):2011-07 |
| | DIN EN 62208 (VDE 0660-511):2012-06 (in parts) |
| Isopropanol (99%) [67-63-0] | Test passed |
| n-Hexane [CAS No. 110-54-3] | Test passed |
| Water + Petroleum ether [CAS No. 64742-82-1] | Test passed |

Testing in a condensation changing climate in the presence of sulfur dioxide

| | |
|---------------|--------------------------|
| Specification | DIN EN ISO 22479:2022-08 |
| Result | Test passed |
| Procedure | Method B |
| Cycles | 2 |

Salt spray test

| | |
|---------------|---|
| Specification | DIN EN IEC 60068-2-11 (VDE 0468-2-11):2022-10 |
| Result | Test passed |

Standards and regulations

| | |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|-----------------|-----------------------------|

Mounting

| | |
|---------------|----------|
| Mounting type | adhesive |
|---------------|----------|

MM-EMLF (EX10)R C1 OG/BK - Label, highly flexible



0803955

<https://www.phoenixcontact.com/us/products/0803955>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27281103 |
| ECLASS-15.0 | 27281103 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC001288 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39131500 |
|-------------|----------|

MM-EMLF (EX10)R C1 OG/BK - Label, highly flexible



0803955

<https://www.phoenixcontact.com/us/products/0803955>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

EF3.1 Climate Change

| | |
|---------|---------------|
| CO2e kg | 0.987 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com