

# THERMOFOX - Thermal transfer printer



0803984

<https://www.phoenixcontact.com/us/products/0803984>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Portable thermal transfer printer for roll material



## Product description

The THERMOFOX handheld printer is ideally suited to fast marking on site. The thermal transfer printer is robust, easy to use, and offers versatile functions. It processes continuous media for terminal blocks, cables and conductors, equipment marking, and plant marking.

## Your advantages

- Maintenance-free operation with proven thermal transfer printer technology
- Printing of self-adhesive, non-sticky labels and shrink sleeves
- The THERMOFOX prints materials in cassette format, which contain the material to be marked and the appropriate ink ribbon.
- 8 different barcodes and over 300 symbols can be integrated.
- Intuitive user guidance thanks to a well-structured menu and direct input keys
- Easy to control with the PROJECT COMPLETE software
- Alternative control via the CLIP PROJECT software

## Commercial data

Item number	0803984
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	BG01
Product key	BG1221
GTIN	4055626212586
Weight per piece (including packing)	835.96 g
Weight per piece (excluding packing)	669.8 g
Customs tariff number	84433210
Country of origin	CN

## Technical data

### Notes

#### Environmental Product Compliance

California Proposition 65

Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration

### Product properties

Product type

Marking system

#### Marking

Identification technology

Thermal transfer

#### Device properties

Print width

24 mm

Print resolution

203 dpi

Operating system

MS Windows 7, MS Windows 8.1, MS Windows 10

### Electrical properties

#### Supply

Supply voltage range

100 V AC ... 240 V AC (50 Hz ... 60 Hz)

### Dimensions

Width

98 mm

Height

69 mm

Length

230 mm

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)

5 °C ... 40 °C

# THERMOFOX - Thermal transfer printer



0803984

<https://www.phoenixcontact.com/us/products/0803984>

## Classifications

### UNSPSC

UNSPSC 21.0	43212108
-------------	----------

# THERMOFOX - Thermal transfer printer



0803984

<https://www.phoenixcontact.com/us/products/0803984>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
-----------------------------------------	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-10
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)