

ESL 60X10 - Insert strip

0804287

<https://www.phoenixcontact.com/us/products/0804287>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Insert strip, Sheet, white (RAL 9010), unmarked, can be labeled with: Office printing systems, CMS-P1-PLOTTER, perforated, mounting type: insert, Number of individual labels: 72, text field height: 10 mm, text field width: 60 mm



Your advantages

- ESL 60x10, white insert label, for marking the UBE/D (60x10) terminal strip marker carrier
- The material file can be downloaded under the PROJECT complete software under Downloads – “Software update – Marking”

Commercial data

Item number	0804287
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BG12
Product key	BG2114
GTIN	4055626291642
Weight per piece (including packing)	14.223 g
Weight per piece (excluding packing)	9.99 g
Customs tariff number	39206219
Country of origin	DE

Technical data

Product properties

Product type	Terminal marker
--------------	-----------------

Marking

Number of individual labels	72
Number of individual labels per row	3

Dimensions

Width	60.00 mm
Height	10.00 mm
Depth	0.20 mm

Text field

Text field width	60 mm
Text field height	10 mm

Material specifications

Color	white (RAL 9010)
Base element material	Polyester
Components	free from silicone and halogen

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)

Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VW PV 3.10.7:2005-02
Result	Test passed

UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
Result	Test passed
Test duration	96 h
Procedure	Artificial irradiation.

Wipe resistance of inscriptions

Specification	IEC 61010-1:2010-06
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropanol (99%) [67-63-0]	Test passed

ESL 60X10 - Insert strip



0804287

<https://www.phoenixcontact.com/us/products/0804287>

n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	DIN EN ISO 22479:2022-08
Result	Test passed
Procedure	Method B
Cycles	2

Salt spray test

Specification	DIN EN IEC 60068-2-11 (VDE 0468-2-11):2022-10
Result	Test passed

Mounting

Mounting type	insert
---------------	--------

ESL 60X10 - Insert strip



0804287

<https://www.phoenixcontact.com/us/products/0804287>

Classifications

ECLASS

ECLASS-13.0	27281106
ECLASS-15.0	27281106

ETIM

ETIM 10.0	EC001288
-----------	----------

UNSPSC

UNSPSC 21.0	39131700
-------------	----------

ESL 60X10 - Insert strip



0804287

<https://www.phoenixcontact.com/us/products/0804287>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com