

PLOTMARK - Marking plotter


0804499

<https://www.phoenixcontact.com/us/products/0804499>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Marking plotter for the entire portfolio of UC marking materials and materials in sheet and strip format.



Product description

Plotting area: 422 x 305 mm, material height: 10.5 mm, plotting speed: 0.04 m/sec, data buffer: 16 MB, resolution: 0.01 mm, repeat accuracy: 0.05 mm

Your advantages

- The plotter is controlled using the PROJECT complete software
- The pens are removed and deposited automatically
- Easily operated with just a few buttons
- The plotter can be connected to the computer quickly and easily via the Centronics or USB interface
- An automatic marking preparation function ensures optimum marking results right from the first character
- During long intervals, the plotter pens are stored safely in a pen station



Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 0804499 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | BG01 |
| Product key | BG1231 |
| GTIN | 4055626381190 |
| Weight per piece (including packing) | 11,469 g |

PLOTMARK - Marking plotter

0804499

<https://www.phoenixcontact.com/us/products/0804499>



| | |
|--------------------------------------|----------|
| Weight per piece (excluding packing) | 8,792 g |
| Customs tariff number | 90171010 |
| Country of origin | DE |

Technical data

Product properties

| | |
|-----------------|-----------------|
| Product type | Marking system |
| Scope of supply | Marking plotter |

Marking

| | |
|---------------------------|---------|
| Identification technology | Plotter |
|---------------------------|---------|

Device properties

| | |
|------------------|---|
| Operating system | MS Windows 7, MS Windows 8.1, MS Windows 10 |
|------------------|---|

Electrical properties

Supply

| | |
|----------------------|---|
| Supply voltage range | 100 V AC ... 240 V AC (50 Hz ... 60 Hz) |
|----------------------|---|

Dimensions

| | |
|--------|--------|
| Width | 480 mm |
| Height | 155 mm |
| Length | 690 mm |

Material specifications

| | |
|------------------------|----------------|
| Color | silver-colored |
| Material Plastic signs | UC |
| | UCT |
| | US |
| | UM |

Environmental and real-life conditions

Ambient conditions

| | |
|--|------------------|
| Ambient temperature (operation) | 10 °C ... 35 °C |
| Ambient temperature (storage/transport) | -10 °C ... 50 °C |
| Permissible humidity (operation) | 35 % ... 75 % |
| Permissible humidity (storage/transport) | 10 % ... 90 % |

PLOTMARK - Marking plotter

0804499

<https://www.phoenixcontact.com/us/products/0804499>



Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 19140201 |
| ECLASS-15.0 | 19140201 |

ETIM

| | |
|----------|----------|
| ETIM 9.0 | EC000610 |
|----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 43212100 |
|-------------|----------|

PLOTMARK - Marking plotter



0804499

<https://www.phoenixcontact.com/us/products/0804499>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com