

# THERMOMARK ROLLMASTER 300 - Thermal transfer printer



0804501

<https://www.phoenixcontact.com/us/products/0804501>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Thermal transfer printer for material off the roll, incl. Euro/US power cable and USB cable. Support CD includes user manuals in several languages, links to firmware, drivers, and planning and marking software. Operating instructions printed in German and English. 1 roll of labels EML (20 x 8)R white = 1000 labels, ink ribbon = 50 m

## Product description

The THERMOMARK ROLLMASTER 300 prints markers in roll format for top quality terminal, wire, cable, equipment, and plant marking applications. You can easily create high-quality printed labels and markers.

## Your advantages

- The THERMOMARK ROLLMASTER 300 is an industrial printer for printing large quantities of marking materials in roll format. Print resolution of 300 dpi.
- Printing of punched and continuous adhesive labels, insert labels, and shrink sleeves
- Fast, high-quality, and durable printing
- Easy and intuitive operation via touch color display
- Maintenance-free operation with proven thermal transfer printer technology
- Easy to control with the PROJECT COMPLETE software
- USB and Ethernet connections

## Commercial data

Item number	0804501
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	BG01
Product key	BG1221
GTIN	4055626381619
Weight per piece (including packing)	13,000 g
Weight per piece (excluding packing)	12,057 g
Customs tariff number	84433210
Country of origin	DE

# THERMOMARK ROLLMASTER 300 - Thermal transfer printer



0804501

<https://www.phoenixcontact.com/us/products/0804501>

## Technical data

### Product properties

Product type	Marking system
Scope of supply	Power cable, USB cable, operating instructions, label roll, ink ribbon

### Marking

Identification technology	Thermotransfer
---------------------------	----------------

### Device properties

Print width	105 mm
Print resolution	300 dpi
Operating system	MS Windows Vista, MS Windows 7 (32/64-bit), MS Windows 8 (32/64-bit), MS Windows 8.1 (32/64-bit), MS Windows 10 (32/64-bit), Server 2008, Server 2008 R2, Server 2012, Server 2012 R2

### Electrical properties

#### Supply

Supply voltage range	100 V AC ... 240 V AC (50 Hz ... 60 Hz)
----------------------	---

### Dimensions

Width	252 mm
Height	288 mm
Length	460 mm

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	10 °C ... 40 °C
---------------------------------	-----------------

# THERMOMARK ROLLMASTER 300 - Thermal transfer printer



0804501

<https://www.phoenixcontact.com/us/products/0804501>

## Classifications

### UNSPSC

UNSPSC 21.0	43212100
-------------	----------

# THERMOMARK ROLLMASTER 300 - Thermal transfer printer



0804501

<https://www.phoenixcontact.com/us/products/0804501>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c), 7(c)-I

### China RoHS

Environment friendly use period (EFUP)	EFUP-10
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)