# TM-RIBBON 110 WH 100 - Ink ribbon

0804661

https://www.phoenixcontact.com/us/products/0804661

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Ink ribbon, For THERMOMARK roll printers and THERMOMARK CARD for printing material-off-the-roll product groups: EML ..., EMLP ..., EMLF ..., PML-M ..., WMTB HF-HP..., WMS-2 HF ... RD and US-material product groups: US-EML(S)P ..., US-EMLP-HA ..., US-EM(S)P ..., US-WMT ..., US-WMTB ..., US-PML-M ..., US-EMLF ..., roll length: 60 m, width: 110 mm, color: white (RAL 9010)

## Commercial data

| | |
|---|---|
| Item number | 0804661 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | BG02 |
| Product key | BG1223 |
| GTIN | 4055626431697 |
| Weight per piece (including packing) | 155.1 g |
| Weight per piece (excluding packing) | 6.956 g |
| Customs tariff number | 96121010 |
| Country of origin | DE |

## Technical data

### Product properties

| | |
|---|---|
| Product type | Ink ribbon |

Marking

| | |
|---|---|
| Identification technology | Thermal transfer |

### Dimensions

| | |
|---|---|
| Width | 110 mm |
| Length of roll | 60 m |

### Material specifications

| | |
|---|---|
| Color | white (RAL 9010) |
| Material | Polyester |

### Environmental and real-life conditions

Ambient conditions

| | |
|---|---|
| Recommended ambient temperature (storage/transport) | 5 °C |
| Recommended humidity (storage/transport) | 30 % |

## Classifications

### ECLASS

| | |
|---|---|
| ECLASS-13.0 | 19140614 |
| ECLASS-15.0 | 19140614 |

### ETIM

| | |
|---|---|
| ETIM 10.0 | EC001694 |

### UNSPSC

| | |
|---|---|
| UNSPSC 21.0 | 44103100 |

## Environmental product compliance

EU RoHS

| | |
|---|---|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |

China RoHS

| | |
|---|---|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|---|---|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com