

# SK 5,08/3,8:UNBEDRUCKT - Marker card



0805412

<https://www.phoenixcontact.com/us/products/0805412>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Marker card, Sheet, white (RAL 9010), unmarked, can be labeled with: Marker pen, mounting type: adhesive, for terminal block width: 5.08 mm, Number of individual labels: 120, text field height: 3.8 mm, text field width: 5.08 mm



## Commercial data

Item number	0805412
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BG05
Product key	BG2113
GTIN	4017918129170
Weight per piece (including packing)	0.91 g
Weight per piece (excluding packing)	0.734 g
Customs tariff number	39199080
Country of origin	PL

## Technical data

### Notes

General	Can be labeled with CMS
---------	-------------------------

### Product properties

Product type	Terminal marker
Pitch	5.08 mm

### Marking

Number of individual labels	120
Number of individual labels per row	10
Number of marker strips	12
Identification technology	manually

### Dimensions

Width	50.00 mm
Height	3.80 mm
Depth	0.07 mm
Pitch	5.08 mm

### Text field

Text field width	5.08 mm
Text field height	3.8 mm

### Material specifications

Foil strength	53 µm
Adhesive strength	20 µm
Adhesive	Acrylic
Color	white (RAL 9010)
Base element material	Polyester
Components	free from silicone and halogen

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 150 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %

#### Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VW PV 3.10.7:2005-02
Result	Test passed

#### UV resistance

0805412

<https://www.phoenixcontact.com/us/products/0805412>

Specification	DIN EN ISO 4892-2:2021-11 (following)
Result	Test passed
Test duration	96 h

## Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-1):2011-07 DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropanol (99%) [67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed

## Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	DIN EN ISO 22479:2022-08
Result	Test passed
Procedure	Method B
Cycles	2

## Salt spray test

Specification	DIN EN IEC 60068-2-11 (VDE 0468-2-11):2022-10
Result	Test passed

## Mounting

Mounting type	adhesive
---------------	----------

0805412

<https://www.phoenixcontact.com/us/products/0805412>

## Classifications

### ECLASS

ECLASS-13.0	27281101
ECLASS-15.0	27281101

### ETIM

ETIM 10.0	EC000761
-----------	----------

### UNSPSC

UNSPSC 21.0	39131500
-------------	----------

0805412

<https://www.phoenixcontact.com/us/products/0805412>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)