

GPE 60X12 WH/R - Engraving material



0807630

<https://www.phoenixcontact.com/us/products/0807630>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Engraving material, Sheet, white (RAL 9010), unmarked, can be labeled with: PLOTMARK, ENGRAVING UNIT, CMS-P1-PLOTTER, P1 ENGRAVING UNIT, mounting type: adhesive, Number of individual labels: 21, text field height: 12 mm, text field width: 60 mm



Your advantages

- Labeling service: Phoenix Contact can custom-label all GPE ... markers according to your requirements
- The adhesive foil used ensures good adhesive properties, even on uneven surfaces
- Two-layer material
- The label sheet consists of prefabricated, individual self-adhesive labels
- Can be engraved using the P1 ENGRAVING UNIT
- Can be labeled easily using the CMS-P1-PLOTTER

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 0807630 |
| Packing unit | 10 pc |
| Minimum order quantity | 1 pc |
| Sales key | BG19 |
| Product key | BG2415 |
| GTIN | 4017918168704 |
| Weight per piece (including packing) | 19.19 g |
| Weight per piece (excluding packing) | 19.57 g |
| Customs tariff number | 39203000 |
| Country of origin | DE |

Technical data

Product properties

| | |
|--------------|---------------|
| Product type | Device marker |
|--------------|---------------|

Marking

| | |
|-------------------------------------|----|
| Number of individual labels | 21 |
| Number of individual labels per row | 7 |

Dimensions

| | |
|--------|----------|
| Width | 60.00 mm |
| Height | 12.00 mm |
| Depth | 0.85 mm |

Text field

| | |
|-------------------|-------|
| Text field width | 60 mm |
| Text field height | 12 mm |

Material specifications

| | |
|-----------------------|--------------------------------|
| Adhesive strength | 50 µm |
| Adhesive | Acrylic |
| Color | white (RAL 9010) |
| Material | TRANSPLY-ABS |
| Base element material | TRANSPLY-ABS |
| Components | free from silicone and halogen |

Environmental and real-life conditions

Ambient conditions

| | |
|---|------------------|
| Ambient temperature (operation) | -20 °C ... 85 °C |
| Recommended ambient temperature (storage/transport) | 20 °C |
| Recommended humidity (storage/transport) | 50 % |

UV resistance

| | |
|---------------|---------------------------------------|
| Specification | DIN EN ISO 4892-2:2021-11 (following) |
| Result | Test passed |
| Procedure | Artificial irradiation. |

Wipe resistance of inscriptions

| | |
|---|-------------------------------------|
| Specification | DIN EN 61010-1 (VDE 0411-1):2011-07 |
| Isopropanol (99%) [67-63-0] | Test passed |
| n-Hexane [CAS No. 110-54-3] | Test passed |
| Water + Petroleum ether [CAS No. 64742-82-1] | Test passed |

Standards and regulations

GPE 60X12 WH/R - Engraving material



0807630

<https://www.phoenixcontact.com/us/products/0807630>

| | |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|-----------------|-----------------------------|

Mounting

| | |
|---------------|----------|
| Mounting type | adhesive |
|---------------|----------|

GPE 60X12 WH/R - Engraving material


0807630

<https://www.phoenixcontact.com/us/products/0807630>



Drawings

Dimensional drawing



GPE 60X12 WH/R - Engraving material



0807630

<https://www.phoenixcontact.com/us/products/0807630>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27281103 |
| ECLASS-15.0 | 27281103 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC001288 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39131500 |
|-------------|----------|

GPE 60X12 WH/R - Engraving material



0807630

<https://www.phoenixcontact.com/us/products/0807630>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com