

# PKBV 200X4,6 - Cable tie

0806660

<https://www.phoenixcontact.com/us/products/0806660>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Steel cable tie, rust-proof, anti-magnetic

## Your advantages

- The stainless steel cable binders are ideal for use with WMTB, KMK 2, and KMK 4 cable markers from Phoenix Contact
- With the UNIFOX-CT ... cable binder tool, the cable binders can be easily tightened and cut off in one step
- UV stabilized (black), for use in outdoor systems
- The cable binders can be used indoors and outdoors even under unfavorable industrial conditions
- For bundling control lines and cables
- Transparent, for standard applications

## Commercial data

Item number	0806660
Packing unit	100 pc
Sales key	B12
Product key	BE7132
GTIN	4017918138707
Weight per piece (including packing)	2.455 g
Weight per piece (excluding packing)	2.455 g
Customs tariff number	73269098
Country of origin	US

# PKBV 200X4,6 - Cable tie



0806660

<https://www.phoenixcontact.com/us/products/0806660>

## Technical data

### Product properties

Product type	Cable tie
Tensile strength GRP	890 N

### Dimensions

Width	4.6 mm
Length	200 mm

### Material specifications

Color	silver-colored
Material	Stainless steel
Components	free from silicone and halogen

### Cable/line

External cable diameter	1 mm ... 63 mm
Tensile strength	890 N

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-80 °C ... 538 °C
Ambient temperature (assembly)	-80 °C ... 538 °C

### Mounting

Mounting type	Cannot be removed
---------------	-------------------

# PKBV 200X4,6 - Cable tie



0806660

<https://www.phoenixcontact.com/us/products/0806660>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)