

# KMV 44X9,6 - Cable marker

0812007

<https://www.phoenixcontact.com/us/products/0812007>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable marker, Stainless steel label, unmarked, can be labeled with: P1 ENGRAVING UNIT, ENGRAVING UNIT, cable diameter range: 1 ... 63 mm, mounting type: Assembly with cable ties, Number of individual labels: 1, text field height: 9 mm, text field width: 23 mm

## Your advantages

- Easy assembly with UNIFOX-CT M7,9
- Secured using stainless steel cable binders
- Cable markers for marking cables and conductors with larger cross sections
- The individual stainless steel markers are pushed onto the corresponding holders

## Commercial data

Item number	0812007
Packing unit	100 pc
Minimum order quantity	100 pc
Sales key	BG19
Product key	BG2415
GTIN	4017918932145
Weight per piece (including packing)	735 MGM
Weight per piece (excluding packing)	735 MGM
Customs tariff number	73269098
Country of origin	US

## Technical data

### Product properties

Product type	Conductor marker
--------------	------------------

### Marking

Number of individual labels	1
-----------------------------	---

### Dimensions

Width	9.60 mm
Height	44.00 mm
Depth	1.00 mm

### Text field

Text field width	23 mm
Text field height	9 mm

### Material specifications

RoHS compliant	yes
Color	silver-colored
Material	Stainless steel
Base element material	Stainless steel

### Cable/line

External cable diameter	1 mm ... 63 mm
-------------------------	----------------

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-80 °C ... 538 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)

#### UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
---------------	---------------------------------------

#### Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-1):2011-07
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)

### Mounting

Mounting type	Assembly with cable ties
---------------	--------------------------

# KMV 44X9,6 - Cable marker



0812007

<https://www.phoenixcontact.com/us/products/0812007>

## Classifications

### ECLASS

ECLASS-13.0	27281102
ECLASS-15.0	27281102

### ETIM

ETIM 10.0	EC001530
-----------	----------

### UNSPSC

UNSPSC 21.0	39131500
-------------	----------

# KMV 44X9,6 - Cable marker



0812007

<https://www.phoenixcontact.com/us/products/0812007>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)