

# SK 10,0 WH:REEL - Marker strip

0812188

<https://www.phoenixcontact.com/us/products/0812188>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Marker strip, Roll, white (RAL 9010), unmarked, can be labeled with: THERMOMARK E.300 (D)/600 (D), THERMOMARK ROLL 2.0, THERMOMARK ROLL, THERMOMARK ROLL X1, THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, mounting type: adhesive, Number of individual labels: 7, text field height: 10 mm, text field width: 90000 mm

## Your advantages

- The self-adhesive marker strips from the SK marking family mark products without a marker groove, ideal for marking COMBICON connectors
- Zack marker strips and flat zack marker strips can be marked subsequently with the SK marking foil
- Quick and inexpensive marking with THERMOMARK ... roll printers from Phoenix Contact
- The thermal transfer printer cutting units make it possible to trim precisely to the required length
- When combined with the right ink ribbon, the marking is highly resistant to solvents and mechanical influences
- The marking is even suitable for use under harsh industrial conditions
- Labeling service: Phoenix Contact can custom-label all SK ... markers in accordance with your requirements
- Labeling service: Phoenix Contact can custom-label all SK ... markers in accordance with your requirements

## Commercial data

Item number	0812188
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BG11
Product key	BG2111
GTIN	4017918951276
Weight per piece (including packing)	1,382 g
Weight per piece (excluding packing)	1,382 g
Customs tariff number	39191080
Country of origin	PL

# SK 10,0 WH:REEL - Marker strip



0812188

<https://www.phoenixcontact.com/us/products/0812188>

## Technical data

### Product properties

Product type	Terminal marker
--------------	-----------------

### Marking

Number of individual labels	7
Number of individual labels per row	1
Number of marker strips	7
Slot type	flat
Identification technology	Thermal transfer

### Dimensions

Width	50.00 mm
Height	10.00 mm
Depth	0.10 mm

### Text field

Text field width	90000 mm
Text field height	10 mm

### Material specifications

Foil strength	53 µm
Adhesive strength	20 µm
Adhesive	Acrylic
Color	white (RAL 9010)
Material	Polyester
Flammability rating according to UL 94	V2
Base element material	Polyester
Components	free from silicone and halogen

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 150 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %

#### Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VW PV 3.10.7:2005-02
Result	Test passed

#### UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
Result	Test passed

# SK 10,0 WH:REEL - Marker strip



0812188

<https://www.phoenixcontact.com/us/products/0812188>

Test duration	96 h
---------------	------

## Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-1):2011-07
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropanol (99%) [67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed

## Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	DIN EN ISO 22479:2022-08
Result	Test passed
Procedure	Method B
Cycles	2

## Salt spray test

Specification	DIN EN IEC 60068-2-11 (VDE 0468-2-11):2022-10
Result	Test passed

## Mounting

Mounting type	adhesive
---------------	----------

# SK 10,0 WH:REEL - Marker strip



0812188

<https://www.phoenixcontact.com/us/products/0812188>

## Classifications

### ECLASS

ECLASS-13.0	27281101
ECLASS-15.0	27281101

### ETIM

ETIM 10.0	EC000761
-----------	----------

### UNSPSC

UNSPSC 21.0	39131500
-------------	----------

# SK 10,0 WH:REEL - Marker strip



0812188

<https://www.phoenixcontact.com/us/products/0812188>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
-----------------------------------------	--------------------

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)