

KMT 24X10 WH 200 - Cable marker



0813925

<https://www.phoenixcontact.com/us/products/0813925>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable marker, Roll, white (RAL 9010), unmarked, can be labeled with: THERMOMARK ROLL, THERMOMARK X1.2, THERMOMARK S1.1, mounting type: Assembly with cable ties, cable diameter: > 10 mm, Number of individual labels: 4000, text field height: 8 mm, text field width: 24 mm

Commercial data

Item number	0813925
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	BG2311
GTIN	4017918958022
Weight per piece (including packing)	656.4 g
Weight per piece (excluding packing)	656.4 g
Country of origin	BE

KMT 24X10 WH 200 - Cable marker



0813925

<https://www.phoenixcontact.com/us/products/0813925>

Technical data

Product properties

Product type	Conductor marker
--------------	------------------

Marking

Number of individual labels	4000
Number of individual labels per row	4
Identification technology	Thermal transfer

Dimensions

Width	24 mm
Height	17 mm
Depth	0.2 mm

Text field

Text field width	24 mm
Text field height	8 mm

Material specifications

Color	white (RAL 9010)
Base element material	Polyester

Cable/line

External cable diameter	> 10.00 mm
-------------------------	------------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 120 °C
Recommended ambient temperature (storage/transport)	27 °C
Recommended humidity (storage/transport)	≤ 60 % (Storage in a dry and dark place in the original packaging is recommended)

Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VDMA 24364:2018-05
Result	Test passed

Scratch resistance

Specification	EN ISO 1518-1:2023 (following)
Requirements	≥ 5 N
Result	Test passed

Tesafilm test

Specification	DIN EN ISO 2409:2020-12 (following)
Result	Test passed

KMT 24X10 WH 200 - Cable marker



0813925

<https://www.phoenixcontact.com/us/products/0813925>

UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
Result	Test passed
Test duration	96 h
Procedure	Artificial irradiation.

Temperature resistance

Specification	ANSI/UL 969-2018:03 (following)
Test duration	240 h
Rating 100 °C (121 °C)	Test passed

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03 DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed
Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2]	Test passed

Immersion in chemicals, oil & fuel

Specification	ISO 175:2010 (following)
Test duration	168 h
Saltwater (saturated 350 g/l) [CAS No. -]	Test passed
Diesel [CAS No. 68476-34-6]	Test passed
IRM 901	Test passed
IRM 902	Test passed
IRM 903	Test passed

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	DIN EN ISO 22479:2022-08
Result	Test passed
Procedure	Method B
Cycles	2

Salt spray test

Specification	DIN EN IEC 60068-2-11 (VDE 0468-2-11):2022-10
Result	Test passed
Test duration	96 h

Mounting

Mounting type	Assembly with cable ties
---------------	--------------------------


KMT 24X10 WH 200 - Cable marker

0813925

<https://www.phoenixcontact.com/us/products/0813925>



Drawings



KMT 24X10 WH 200 - Cable marker



0813925

<https://www.phoenixcontact.com/us/products/0813925>

Classifications

ECLASS

ECLASS-13.0	27281102
ECLASS-15.0	27281102

ETIM

ETIM 10.0	EC001530
-----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

KMT 24X10 WH 200 - Cable marker



0813925

<https://www.phoenixcontact.com/us/products/0813925>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com