

ZBF 5:UNBEDRUCKT - Zack Marker strip, flat



0808642

<https://www.phoenixcontact.com/us/products/0808642>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Zack Marker strip, flat, Strip, white (RAL 9010), unmarked, can be labeled with: PLOTMARK, CMS-P1-PLOTTER, mounting type: latching, for terminal block width: 5 mm, Number of individual labels: 10, text field height: 5.15 mm, text field width: 5.15 mm

Your advantages

- Unmarked marking strips can be custom-labeled with a plotter or by hand
- Other pitches available on request
- The ZBF zack marker strip system with flat marker groove is a marking solution for modular terminal blocks and electronics modules
- The multi-section marking strips are easy to fit and can be easily separated if required

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 0808642 |
| Packing unit | 10 pc |
| Minimum order quantity | 10 pc |
| Sales key | BG05 |
| Product key | BG2112 |
| GTIN | 4017918180355 |
| Weight per piece (including packing) | 0.61 g |
| Weight per piece (excluding packing) | 0.315 g |
| Customs tariff number | 39269097 |
| Country of origin | DE |

ZBF 5:UNBEDRUCKT - Zack Marker strip, flat



0808642

<https://www.phoenixcontact.com/us/products/0808642>

Technical data

Product properties

| | |
|--------------|-----------------|
| Product type | Terminal marker |
| Pitch | 5 mm |

Marking

| | |
|-------------------------------------|------|
| Number of individual labels | 10 |
| Number of individual labels per row | 10 |
| Number of marker strips | 10 |
| Slot type | flat |

Dimensions

| | |
|--------|---------|
| Width | 5.15 mm |
| Height | 6.40 mm |
| Depth | 1.60 mm |
| Pitch | 5 mm |

Text field

| | |
|-------------------|---------|
| Text field width | 5.15 mm |
| Text field height | 5.15 mm |

Material specifications

| | |
|--|--------------------------------|
| Color | white (RAL 9010) |
| Material | PA |
| Flammability rating according to UL 94 | V2 |
| Base element material | PA |
| Components | free from silicone and halogen |

Environmental and real-life conditions

Ambient conditions

| | |
|---|-------------------|
| Ambient temperature (operation) | -40 °C ... 100 °C |
| Recommended ambient temperature (storage/transport) | 23 °C |
| Recommended humidity (storage/transport) | 50 % |

UV resistance

| | |
|---------------|---------------------------------------|
| Specification | DIN EN ISO 4892-2:2021-11 (following) |
|---------------|---------------------------------------|

Wipe resistance of inscriptions

| | |
|---------------|--|
| Specification | DIN EN 61010-1 (VDE 0411-1):2011-07 |
| | DIN EN 62208 (VDE 0660-511):2012-06 (in parts) |

Standards and regulations

| | |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|-----------------|-----------------------------|

ZBF 5:UNBEDRUCKT - Zack Marker strip, flat



0808642

<https://www.phoenixcontact.com/us/products/0808642>

Mounting

Mounting type

latching

ZBF 5:UNBEDRUCKT - Zack Marker strip, flat

0808642

<https://www.phoenixcontact.com/us/products/0808642>

Drawings

Schematic diagram



ZBF 5:UNBEDRUCKT - Zack Marker strip, flat



0808642

<https://www.phoenixcontact.com/us/products/0808642>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27281101 |
| ECLASS-15.0 | 27281101 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC000761 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39131500 |
|-------------|----------|

ZBF 5:UNBEDRUCKT - Zack Marker strip, flat



0808642

<https://www.phoenixcontact.com/us/products/0808642>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

EF3.1 Climate Change

| | |
|---------|---------------|
| CO2e kg | 0.005 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com