

ZBF 5,LGS:L1-N,PE - Zack marker strip

0809528

<https://www.phoenixcontact.com/us/products/0809528>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Zack marker strip, Strip, white (RAL 9010), labeled, printed horizontally: L1, L2, L3, N, PE, L1, L2, L3, N, PE, mounting type: latching, for terminal block width: 5 mm, Number of individual labels: 10, text field height: 5.15 mm, text field width: 5.15 mm

Commercial data

Item number	0809528
Packing unit	10 pc
Minimum order quantity	10 pc
Product key	BG2122
GTIN	4017918607418
Weight per piece (including packing)	0.53 g
Weight per piece (excluding packing)	0.53 g
Country of origin	DE

ZBF 5,LGS:L1-N,PE - Zack marker strip



0809528

<https://www.phoenixcontact.com/us/products/0809528>

Technical data

Product properties

Product type	Terminal marker
Pitch	5 mm

Marking

Number of individual labels	10
Number of individual labels per row	10
Number of marker strips	10
Printing direction	printed horizontally
Printing	L1, L2, L3, N, PE, L1, L2, L3, N, PE
Slot type	flat

Dimensions

Width	5.15 mm
Height	6.40 mm
Depth	1.60 mm
Pitch	5 mm

Text field

Text field width	5.15 mm
Text field height	5.15 mm

Material specifications

Color	white (RAL 9010)
Material	PA
Flammability rating according to UL 94	V2
Base element material	PA
Components	free from silicone and halogen

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)

Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VW PV 3.10.7:2005-02
Result	Test passed

Scratch resistance

Specification	EN ISO 1518-1:2023 (following)
---------------	--------------------------------

ZBF 5,LGS:L1-N,PE - Zack marker strip



0809528

<https://www.phoenixcontact.com/us/products/0809528>

Requirements	≥ 5 N
Result	Test passed

Tesafilm test

Specification	DIN EN ISO 2409:2020-12 (following)
Result	Test passed

UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
Result	Test passed
Test duration	96 h
Procedure	Artificial irradiation.

Temperature storage

Specification	IEC 60068-2-2:2007-07
Result	Test passed
Procedure	Test Bb
Duration	96 h
Temperature for testing	120 °C

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03 DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropanol (99%) [67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	EN ISO 22479:2022-06
Result	Test passed
Procedure	Method B
Cycles	2

Salt spray test

Specification	DIN EN IEC 60068-2-11 (VDE 0468-2-11):2022-10
Result	Test passed
Test duration	96 h

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Mounting

Mounting type	latching
---------------	----------

ZBF 5,LGS:L1-N,PE - Zack marker strip

0809528

<https://www.phoenixcontact.com/us/products/0809528>



Drawings

Schematic diagram



ZBF 5,LGS:L1-N,PE - Zack marker strip



0809528

<https://www.phoenixcontact.com/us/products/0809528>

Classifications

ECLASS

ECLASS-13.0	27281101
ECLASS-15.0	27281101

ETIM

ETIM 10.0	EC000761
-----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

ZBF 5,LGS:L1-N,PE - Zack marker strip



0809528

<https://www.phoenixcontact.com/us/products/0809528>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	0.005 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com