

SK 10,0 WH:REEL - Marker strip



0812188

<https://www.phoenixcontact.com/us/products/0812188>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Marker strip, Roll, white (RAL 9010), unmarked, can be labeled with: THERMOMARK E.300 (D)/600 (D), THERMOMARK ROLL 2.0, THERMOMARK ROLL, THERMOMARK ROLL X1, THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, mounting type: adhesive, Number of individual labels: 7, text field height: 10 mm, text field width: 90000 mm

Your advantages

- The self-adhesive marker strips from the SK marking family mark products without a marker groove, ideal for marking COMBICON connectors
- Zack marker strips and flat zack marker strips can be marked subsequently with the SK marking foil
- Quick and inexpensive marking with THERMOMARK ... roll printers from Phoenix Contact
- The thermal transfer printer cutting units make it possible to trim precisely to the required length
- When combined with the right ink ribbon, the marking is highly resistant to solvents and mechanical influences
- The marking is even suitable for use under harsh industrial conditions
- Labeling service: Phoenix Contact can custom-label all SK ... markers in accordance with your requirements
- Labeling service: Phoenix Contact can custom-label all SK ... markers in accordance with your requirements

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 0812188 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | BG11 |
| Product key | BG2111 |
| GTIN | 4017918951276 |
| Weight per piece (including packing) | 1,382 g |
| Weight per piece (excluding packing) | 1,382 g |
| Customs tariff number | 39191080 |
| Country of origin | PL |

SK 10,0 WH:REEL - Marker strip



0812188

<https://www.phoenixcontact.com/us/products/0812188>

Technical data

Product properties

| | |
|--------------|-----------------|
| Product type | Terminal marker |
|--------------|-----------------|

Marking

| | |
|-------------------------------------|------------------|
| Number of individual labels | 7 |
| Number of individual labels per row | 1 |
| Number of marker strips | 7 |
| Slot type | flat |
| Identification technology | Thermal transfer |

Dimensions

| | |
|--------|----------|
| Width | 50.00 mm |
| Height | 10.00 mm |
| Depth | 0.10 mm |

Text field

| | |
|-------------------|----------|
| Text field width | 90000 mm |
| Text field height | 10 mm |

Material specifications

| | |
|--|--------------------------------|
| Foil strength | 53 µm |
| Adhesive strength | 20 µm |
| Adhesive | Acrylic |
| Color | white (RAL 9010) |
| Material | Polyester |
| Flammability rating according to UL 94 | V2 |
| Base element material | Polyester |
| Components | free from silicone and halogen |

Environmental and real-life conditions

Ambient conditions

| | |
|---|-------------------|
| Ambient temperature (operation) | -40 °C ... 150 °C |
| Recommended ambient temperature (storage/transport) | 23 °C |
| Recommended humidity (storage/transport) | 50 % |

Test for substances that would hinder coating with paint or varnish

| | |
|---|----------------------|
| Testing for paint wetting impairment substances (LABS-conformity) | VW PV 3.10.7:2005-02 |
| Result | Test passed |

UV resistance

| | |
|---------------|---------------------------------------|
| Specification | DIN EN ISO 4892-2:2021-11 (following) |
| Result | Test passed |

SK 10,0 WH:REEL - Marker strip



0812188

<https://www.phoenixcontact.com/us/products/0812188>

| | |
|---------------|------|
| Test duration | 96 h |
|---------------|------|

Wipe resistance of inscriptions

| | |
|---|--|
| Specification | DIN EN 61010-1 (VDE 0411-1):2011-07 |
| | DIN EN 62208 (VDE 0660-511):2012-06 (in parts) |
| Isopropanol (99%) [67-63-0] | Test passed |
| n-Hexane [CAS No. 110-54-3] | Test passed |
| Water + Petroleum ether [CAS No. 64742-82-1] | Test passed |

Testing in a condensation changing climate in the presence of sulfur dioxide

| | |
|---------------|--------------------------|
| Specification | DIN EN ISO 22479:2022-08 |
| Result | Test passed |
| Procedure | Method B |
| Cycles | 2 |

Salt spray test

| | |
|---------------|---|
| Specification | DIN EN IEC 60068-2-11 (VDE 0468-2-11):2022-10 |
| Result | Test passed |

Mounting

| | |
|---------------|----------|
| Mounting type | adhesive |
|---------------|----------|

SK 10,0 WH:REEL - Marker strip



0812188

<https://www.phoenixcontact.com/us/products/0812188>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27281101 |
| ECLASS-15.0 | 27281101 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC000761 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39131500 |
|-------------|----------|

SK 10,0 WH:REEL - Marker strip



0812188

<https://www.phoenixcontact.com/us/products/0812188>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com