

# EMT (44X7)R - Insert label

0819275

<https://www.phoenixcontact.com/us/products/0819275>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Insert label, Roll, white (RAL 9010), unmarked, can be labeled with: THERMOMARK E.300 (D)/600 (D), THERMOMARK ROLL 2.0, THERMOMARK ROLL, THERMOMARK ROLL X1, THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, cable diameter range: 16 ... 35 mm, mounting type: insert, Number of individual labels: 500, text field height: 7 mm, text field width: 44 mm

## Your advantages

- Marker strips for KLM-A terminal strip marker carriers
- Thanks to their special shape, the EMT (44x7)R insert labels remain securely inside the carrier once inserted
- Quick and inexpensive marking with THERMOMARK ... roll printers from Phoenix Contact
- When combined with the right ink ribbon, the marking is highly resistant to solvents and mechanical influences
- Marking service: Phoenix Contact can custom-mark all EMT ... markers according to your requirements

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 0819275       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | BG17          |
| Product key                          | BG2111        |
| GTIN                                 | 4046356141185 |
| Weight per piece (including packing) | 161 g         |
| Weight per piece (excluding packing) | 166.8 g       |
| Customs tariff number                | 39269097      |
| Country of origin                    | DE            |

# EMT (44X7)R - Insert label



0819275

<https://www.phoenixcontact.com/us/products/0819275>

## Technical data

### Product properties

|              |               |
|--------------|---------------|
| Product type | Device marker |
|--------------|---------------|

### Marking

|                                     |                  |
|-------------------------------------|------------------|
| Number of individual labels         | 500              |
| Number of individual labels per row | 2                |
| Identification technology           | Thermal transfer |

### Dimensions

|        |          |
|--------|----------|
| Width  | 44.00 mm |
| Height | 6.50 mm  |
| Depth  | 0.35 mm  |

### Text field

|                   |       |
|-------------------|-------|
| Text field width  | 44 mm |
| Text field height | 7 mm  |

### Material specifications

|                       |                                |
|-----------------------|--------------------------------|
| Foil strength         | 125 µm                         |
| Color                 | white (RAL 9010)               |
| Base element material | Polyester                      |
| Components            | free from silicone and halogen |

### Cable/line

|                         |                 |
|-------------------------|-----------------|
| External cable diameter | 16 mm ... 35 mm |
|-------------------------|-----------------|

### Environmental and real-life conditions

#### Ambient conditions

|   |   |
|---|---|
| Ambient temperature (operation)                     | -40 °C ... 150 °C   |
| Recommended ambient temperature (storage/transport) | 23 °C   |
| Recommended humidity (storage/transport)            | 50 % (Storage in a dry and dark place in the original packaging is recommended) |

#### Test for substances that would hinder coating with paint or varnish

|   |                         |
|---|-------------------------|
| Testing for paint wetting impairment substances (LABS-conformity) | VDMA 24364-A1-L:2018-05 |
| Result  | Test passed             |

#### Test for substances that would hinder coating with paint or varnish

|   |                      |
|---|----------------------|
| Testing for paint wetting impairment substances (LABS-conformity) | VW PV 3.10.7:2005-02 |
| Result  | Test passed          |

### Scratch resistance

# EMT (44X7)R - Insert label



0819275

<https://www.phoenixcontact.com/us/products/0819275>

|               |                                |
|---------------|--------------------------------|
| Specification | EN ISO 1518-1:2023 (following) |
| Requirements  | ≥ 5 N                          |
| Result        | Test passed                    |

## Tesafilem test

|               |                                     |
|---------------|-------------------------------------|
| Specification | DIN EN ISO 2409:2020-12 (following) |
| Result        | Test passed                         |

## UV resistance

|               |                                       |
|---------------|---------------------------------------|
| Specification | DIN EN ISO 4892-2:2021-11 (following) |
| Result        | Test passed                           |
| Test duration | 96 h                                  |
| Procedure     | Artificial irradiation.               |

## Temperature storage

|                         |                       |
|-------------------------|-----------------------|
| Specification           | IEC 60068-2-2:2007-07 |
| Result                  | Test passed           |
| Procedure               | Test Bb               |
| Duration                | 96 h                  |
| Temperature for testing | 120 °C                |

## Temperature resistance

|                        |                                 |
|------------------------|---------------------------------|
| Specification          | ANSI/UL 969-2018:03 (following) |
| Test duration          | 240 h                           |
| Rating 150 °C (180 °C) | Test passed                     |

## Wipe resistance of inscriptions

|   |  |
|---|--|
| Specification                                     | DIN EN 61010-1 (VDE 0411-01):2020-03<br>DIN EN 62208 (VDE 0660-511):2012-06 (in parts) |
| Isopropanol (99%) [67-63-0]                       | Test passed  |
| n-Hexane<br>[CAS No. 110-54-3]                    | Test passed  |
| Water + Petroleum ether<br>[CAS No. 64742-82-1]   | Test passed  |
| Sodium hydroxide 0.1 mol/l<br>[CAS No. 1310-73-2] | Test passed  |
| Ethanol (99 %)<br>[CAS No. 64-17-5]               | Test passed  |

## Immersion in chemicals, oil & fuel

|   |                          |
|---|--------------------------|
| Specification                                     | ISO 175:2010 (following) |
| Test duration                                     | 168 h                    |
| Sodium hydroxide 0.1 mol/l<br>[CAS No. 1310-73-2] | Test passed              |
| Saltwater (saturated 350 g/l)<br>[CAS No. - ]     | Test passed              |
| Ethanol (99 %)<br>[CAS No. 64-17-5]               | Test passed              |

# EMT (44X7)R - Insert label



0819275

<https://www.phoenixcontact.com/us/products/0819275>

|                                  |             |
|----------------------------------|-------------|
| Gasoline<br>[CAS No. 64742-49-0] | Test passed |
| Diesel<br>[CAS No. 68476-34-6]   | Test passed |
| IRM 901                          | Test passed |
| IRM 902                          | Test passed |
| IRM 903                          | Test passed |

## Testing in a condensation changing climate in the presence of sulfur dioxide

|               |                      |
|---------------|----------------------|
| Specification | EN ISO 22479:2022-06 |
| Result        | Test passed          |
| Procedure     | Method B             |
| Cycles        | 2                    |

## Salt spray test

|               |   |
|---------------|---|
| Specification | DIN EN IEC 60068-2-11 (VDE 0468-2-11):2022-10 |
| Result        | Test passed                                   |
| Test duration | 96 h  |

## Mounting

|               |        |
|---------------|--------|
| Mounting type | insert |
|---------------|--------|

# EMT (44X7)R - Insert label



0819275

<https://www.phoenixcontact.com/us/products/0819275>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27281106 |
| ECLASS-15.0 | 27281106 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC001288 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39131700 |
|-------------|----------|

# EMT (44X7)R - Insert label



0819275

<https://www.phoenixcontact.com/us/products/0819275>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)