

EMLP 24 (30X12)R SR - Plastic label with drill hole



0819563

<https://www.phoenixcontact.com/us/products/0819563>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Plastic label with drill hole, Roll, unmarked, can be labeled with: THERMOMARK E.300 (D)/600 (D), THERMOMARK ROLL 2.0, THERMOMARK ROLL, THERMOMARK ROLL X1, THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, mounting type: adhesive, Number of individual labels: 500, text field height: 12 mm, text field width: 30 mm

Your advantages

- The EMLP ... self-adhesive markers are particularly suited to marking electrical components, devices, and buttons
- The markers meet the same standards as the engraved labels, they provide high-quality visuals
- Quick and inexpensive marking with THERMOMARK ... roll printers from Phoenix Contact
- When combined with the right ink ribbon, the marking is highly resistant to solvents and mechanical influences
- Labeling service: Phoenix Contact can custom-label all EMLP ... markers in accordance with your requirements

Commercial data

Item number	0819563
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BG16
Product key	BG2411
GTIN	4046356160711
Weight per piece (including packing)	415 g
Weight per piece (excluding packing)	210.08 g
Customs tariff number	39269097
Country of origin	DE

EMLP 24 (30X12)R SR - Plastic label with drill hole



0819563

<https://www.phoenixcontact.com/us/products/0819563>

Technical data

Product properties

Product type	Device marker
--------------	---------------

Marking

Number of individual labels	500
Number of individual labels per row	2
Identification technology	Thermal transfer

Dimensions

Width	30.00 mm
Height	40.00 mm
Depth	0.55 mm

Text field

Text field width	30 mm
Text field height	12 mm

Material specifications

RoHS compliant	yes
Foil strength	175 µm
Adhesive strength	400 µm
Adhesive	Acrylic
Color	silver-colored
Material	Polyester
Base element material	Polyester
Components	Silicone-free

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 120 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)

Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VDMA 24364-A1-L:2018-05
Result	Test passed

Scratch resistance

Specification	DIN EN ISO 1518-1:2019-10 (following)
Requirements	≥ 5 N
Result	Test passed

EMLP 24 (30X12)R SR - Plastic label with drill hole



0819563

<https://www.phoenixcontact.com/us/products/0819563>

Tesafilm test

Specification	DIN EN ISO 2409:2013 (following)
Result	Test passed

UV resistance

Specification	ISO 4892-2:2013-03 (following)
Result	Test passed
Test duration	96 h
Procedure	Artificial irradiation.

Temperature resistance

Specification	ANSI/UL 969-2018:03 (following)
Test duration	240 h
Rating 150 °C (180 °C)	Test passed

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03 DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropanol (99%) [67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed
Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2]	Test passed
Ethanol (99 %) [CAS No. 64-17-5]	Test passed

Immersion in chemicals, oil & fuel

Specification	ISO 175:2010 (following)
Test duration	168 h
Saltwater (saturated 350 g/l) [CAS No. -]	Test passed
Diesel [CAS No. 68476-34-6]	Test passed
IRM 901	Test passed
IRM 902	Test passed
IRM 903	Test passed

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	EN ISO 22479:2022-06
Result	Test passed
Cycles	2

Salt spray test

Specification	DIN EN IEC 60068-2-11 (VDE 0468-2-11):2022-10
Result	Test passed
Test duration	96 h

EMLP 24 (30X12)R SR - Plastic label with drill hole



0819563

<https://www.phoenixcontact.com/us/products/0819563>

Standards and regulations

Wipe resistance

DIN EN 61010-1 (VDE 0411-1)

Mounting

Mounting type

adhesive

EMLP 24 (30X12)R SR - Plastic label with drill hole



0819563

<https://www.phoenixcontact.com/us/products/0819563>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/0819563>



cULus Recognized

Approval ID: MH48542-20251115

EMLP 24 (30X12)R SR - Plastic label with drill hole



0819563

<https://www.phoenixcontact.com/us/products/0819563>

Classifications

ECLASS

ECLASS-13.0	27281103
ECLASS-15.0	27281103

ETIM

ETIM 10.0	EC001288
-----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

EMLP 24 (30X12)R SR - Plastic label with drill hole



0819563

<https://www.phoenixcontact.com/us/products/0819563>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com