

WMSHF 25 (EX40)R YE - Shrink sleeve



0822136

<https://www.phoenixcontact.com/us/products/0822136>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Shrink sleeve, Roll, unmarked, can be labeled with: THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, THERMOMARK ROLL X1, THERMOMARK ROLL 2.0, THERMOMARK ROLL, THERMOMARK W, cable diameter range: 8 ... 25 mm, unperforated, mounting type: slide-on

Commercial data

Item number	0822136
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	BG14
Product key	BG2216
GTIN	4046356448505
Weight per piece (including packing)	464 g
Weight per piece (excluding packing)	464 g
Customs tariff number	39173200
Country of origin	CN

WMSHF 25 (EX40)R YE - Shrink sleeve



0822136

<https://www.phoenixcontact.com/us/products/0822136>

Technical data

Product properties

Product type	Shrink sleeve
--------------	---------------

Marking

Identification technology	Thermotransfer
---------------------------	----------------

Dimensions

Width	40 mm
Length	15 m

Material specifications

Color	yellow
Components	halogen-free

Cable/line

External cable diameter	8 mm ... 25 mm
-------------------------	----------------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-55 °C ... 125 °C
---------------------------------	-------------------

Mounting

Mounting type	slide-on
---------------	----------

WMSHF 25 (EX40)R YE - Shrink sleeve



0822136

<https://www.phoenixcontact.com/us/products/0822136>

Environmental product compliance

EU REACH SVHC

REACH candidate substance (CAS No.)	
-------------------------------------	--

	No substance above 0.1 wt%
--	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com