

# UC-EMLP (60X30) YE - Plastic label

0822657

<https://www.phoenixcontact.com/us/products/0822657>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Plastic label, Sheet, yellow (RAL 1018), unmarked, can be labeled with: BLUEMARK E.CARD, BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, PLOTMARK, CMS-P1-PLOTTER, mounting type: adhesive, Number of individual labels: 3, text field height: 30 mm, text field width: 60 mm

## Your advantages

- The markers, which are supplied in uniform sheets, can be printed onto quickly and easily using the BLUEMARK printing system
- The UC-EMLP ... UniCard marking range includes self-adhesive device markers with good adhesive properties
- The sheets provide additional space for project information and function text that can be helpful during further assembly
- The multi-section marking strips are easy to fit and can be easily separated if required
- Marking service: Phoenix Contact can custom-mark all UniCard markers according to your specifications

## Commercial data

Item number	0822657
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BG10
Product key	BG2417
GTIN	4046356328616
Weight per piece (including packing)	13.618 g
Weight per piece (excluding packing)	14 g
Customs tariff number	39269097
Country of origin	PL

# UC-EMLP (60X30) YE - Plastic label



0822657

<https://www.phoenixcontact.com/us/products/0822657>

## Technical data

### Product properties

Product type	Device marker
--------------	---------------

### Marking

Number of individual labels	3
Number of individual labels per row	1
Identification technology	UV LED technology

### Dimensions

Width	60.00 mm
Height	30.00 mm
Depth	1.20 mm

### Text field

Text field width	60 mm
Text field height	30 mm

### Material specifications

Adhesive strength	250 µm
Adhesive	Acrylic
Color	yellow (RAL 1018)
Material	PA
Flammability rating according to UL 94	V2
Base element material	PA
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 2
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 2
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 2
Components	free from silicone and halogen

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)

#### Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VDMA 24364-A1-L:2018-05
Result	Test passed

#### Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VW PV 3.10.7:2005-02
---	----------------------

# UC-EMLP (60X30) YE - Plastic label



0822657

<https://www.phoenixcontact.com/us/products/0822657>

Result	Test passed
--------	-------------

## Scratch resistance

Specification	EN ISO 1518-1:2023 (following)
Requirements	≥ 5 N
Result	Test passed

## Tesafilm test

Specification	DIN EN ISO 2409:2020-12 (following)
Result	Test passed

## UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
Result	Test passed
Test duration	96 h
Procedure	Artificial irradiation.

## Temperature resistance

Specification	ANSI/UL 969-2018:03 (following)
Test duration	240 h
Rating 100 °C (121 °C)	Test passed

## Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03 DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropanol (99%) [67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed
Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2]	Test passed
Ethanol (99 %) [CAS No. 64-17-5]	Test passed

## Immersion in chemicals, oil & fuel

Specification	ISO 175:2010 (following)
Test duration	168 h
Saltwater (saturated 350 g/l) [CAS No. - ]	Test passed
Diesel [CAS No. 68476-34-6]	Test passed
IRM 901	Test passed
IRM 902	Test passed
IRM 903	Test passed

## Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	EN ISO 22479:2022-06
Result	Test passed

# UC-EMLP (60X30) YE - Plastic label



0822657

<https://www.phoenixcontact.com/us/products/0822657>

Procedure	Method B
Cycles	2

## Salt spray test

Specification	DIN EN IEC 60068-2-11 (VDE 0468-2-11):2022-10
Result	Test passed
Test duration	96 h

## Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

## Standards

Standards/regulations	EN 45545-2
-----------------------	------------

## Mounting

Mounting type	adhesive
---------------	----------

# UC-EMLP (60X30) YE - Plastic label



0822657

<https://www.phoenixcontact.com/us/products/0822657>

## Classifications

### ECLASS

ECLASS-13.0	27281103
ECLASS-15.0	27281103

### ETIM

ETIM 10.0	EC001288
-----------	----------

### UNSPSC

UNSPSC 21.0	39131500
-------------	----------

# UC-EMLP (60X30) YE - Plastic label



0822657

<https://www.phoenixcontact.com/us/products/0822657>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

### EF3.1 Climate Change

CO2e kg	0.27 kg CO2e
---------	--------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)