

# BMK 20X 8 WH CUS - Fabric label sheet




0824231

<https://www.phoenixcontact.com/us/products/0824231>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Fabric label sheet, can be ordered: in sheets, white (RAL 9010), labeled according to customer specifications, mounting type: adhesive, Number of individual labels: 270



## Your advantages

- Available in various dimensions
- Self-adhesive labels for labeling by hand or with a plotter
- Secure adhesion even on curved or uneven surfaces as well as round corners
- Labeling service: Phoenix Contact can custom-label all BMK ... markers according to your requirements

## Commercial data

Item number	0824231
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	BG8144
GTIN	4046356351096
Weight per piece (including packing)	10 g
Weight per piece (excluding packing)	9 g
Country of origin	PL

## Technical data

### Product properties

Product type	Device marker
--------------	---------------

### Marking

Number of individual labels	270
Identification technology	Plotter

### Dimensions

Width	20 mm
Length	8 mm

### Material specifications

Adhesive	Acrylic
Color	white (RAL 9010)
Material	Polyester foil
Base element material	Polyester foil
Components	Silicone-free

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 80 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %

#### Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VW PV 3.10.7:2005-02
Result	Test passed

#### UV resistance

Specification	ISO 4892-2:2013-03 (following)
Result	Test passed
Test duration	96 h

#### Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-1):2011-07
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropanol (99%) [67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed

#### Testing in a condensation changing climate in the presence of sulfur dioxide

# BMK 20X 8 WH CUS - Fabric label sheet



0824231

<https://www.phoenixcontact.com/us/products/0824231>

Specification	DIN 50018:2013-05
Result	Test passed
Climate level	AHT 1.0 S
Cycles	2

## Salt spray test

Specification	DIN EN 60068-2-11:2000-02
Result	Test passed

## Mounting

Mounting type	adhesive
---------------	----------

# BMK 20X 8 WH CUS - Fabric label sheet



0824231

<https://www.phoenixcontact.com/us/products/0824231>

## Classifications

### UNSPSC

UNSPSC 21.0	39131500
-------------	----------

# BMK 20X 8 WH CUS - Fabric label sheet



0824231

<https://www.phoenixcontact.com/us/products/0824231>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)