

EMLC (5,5X40)R CUS - Fabric label



0824351

<https://www.phoenixcontact.com/us/products/0824351>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Fabric label, Roll, can be ordered: by line, white (RAL 9010), labeled according to customer specifications, mounting type: adhesive, Number of individual labels: 12, text field height: 40 mm, text field width: 5.5 mm

Your advantages

- The EMLC label consists of a textile foil with very low restoring forces
- Enables labels to be stuck over edges and curves
- Labeling service: Phoenix Contact can custom-label all EMLC ... markers in accordance with your requirements

Commercial data

Item number	0824351
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	BG8141
GTIN	4046356352277
Weight per piece (including packing)	0.78 g
Weight per piece (excluding packing)	0.78 g
Country of origin	PL

EMLC (5,5X40)R CUS - Fabric label



0824351

<https://www.phoenixcontact.com/us/products/0824351>

Technical data

Product properties

Product type	Device marker
Product property	Low restoring force

Marking

Number of individual labels	12
Number of individual labels per row	12
Identification technology	Thermal transfer

Dimensions

Width	40.00 mm
Height	5.50 mm
Depth	0.15 mm
Length	40 mm

Text field

Text field width	5.5 mm
Text field height	40 mm

Material specifications

Foil strength	130 µm
Adhesive strength	28 µm
Adhesive	Acrylic
Color	white (RAL 9010)
Material	PA
Base element material	PA
Components	free from silicone and halogen

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	0 °C ... 125 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)

Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VW PV 3.10.7:2005-02
Result	Test passed

Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VDMA 24364:2018-05
Result	Test passed

EMLC (5,5X40)R CUS - Fabric label



0824351

<https://www.phoenixcontact.com/us/products/0824351>

Scratch resistance

Specification	EN ISO 1518-1:2023 (following)
Requirements	≥ 5 N
Result	Test passed

Tesafilm test

Specification	DIN EN ISO 2409:2020-12 (following)
Result	Test passed

UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
Result	Test passed
Test duration	96 h
Procedure	Artificial irradiation.

Moisture heat storage

Specification	IEC 60068-2-78:2012-10 (following)
Result	Test passed
Duration	96 h
Temperature for testing	40 °C
Relative humidity	93 %

Temperature resistance

Specification	ANSI/UL 969-2018:03 (following)
Test duration	240 h
Rating 125 °C (150 °C)	Test passed

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03 DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropanol (99%) [67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed
Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2]	Test passed
Acetone (99 %) [CAS No. 67-64-1]	Test passed

Immersion in chemicals, oil & fuel

Specification	ISO 175:2010 (following)
Test duration	168 h
Saltwater (saturated 350 g/l) [CAS No. -]	Test passed
Diesel [CAS No. 68476-34-6]	Test passed
IRM 901	Test passed

EMLC (5,5X40)R CUS - Fabric label



0824351

<https://www.phoenixcontact.com/us/products/0824351>

IRM 902	Test passed
IRM 903	Test passed

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	DIN EN ISO 22479:2022-08
Result	Test passed
Procedure	Method B
Cycles	2

Salt spray test

Specification	DIN EN IEC 60068-2-11 (VDE 0468-2-11):2022-10
Result	Test passed
Test duration	96 h

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Mounting

Mounting type	adhesive
---------------	----------

EMLC (5,5X40)R CUS - Fabric label



0824351

<https://www.phoenixcontact.com/us/products/0824351>

Classifications

ECLASS

ECLASS-13.0	27281103
ECLASS-15.0	27281103

ETIM

ETIM 10.0	EC001288
-----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

EMLC (5,5X40)R CUS - Fabric label



0824351

<https://www.phoenixcontact.com/us/products/0824351>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com