


# PABA BU/15 CUS - Cable marker



0824441

<https://www.phoenixcontact.com/us/products/0824441>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable marker, can be ordered: Strip, blue (RAL 5015), labeled according to customer specifications, cable diameter range: 0.6 ... 50 mm, mounting type: thread on

## Commercial data

Item number	0824441
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	BG8123
GTIN	4046356353090
Weight per piece (including packing)	4.561 g
Weight per piece (excluding packing)	4.5 g
Country of origin	PL

0824441

<https://www.phoenixcontact.com/us/products/0824441>

## Technical data

### Product properties

Product type	Conductor marker
--------------	------------------

### Marking

Identification technology	Plotter
---------------------------	---------

### Dimensions

Width	15 mm
Length	4 mm

### Material specifications

Color	blue (RAL 5015)
Material	ABS
Flammability rating according to UL 94	V0

### Cable/line

External cable diameter	0.6 mm ... 50 mm
-------------------------	------------------

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-15 °C ... 65 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)

#### Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VDMA 24364-A1-L:2018-05
Result	Test passed

#### Scratch resistance

Specification	DIN EN ISO 1518-1:2019-10 (following)
Requirements	≥ 5 N
Result	Test passed

#### Tesafilm test

Specification	DIN EN ISO 2409:2013 (following)
Result	Test passed

#### UV resistance

Specification	ISO 4892-2:2013-03 (following)
Result	Test passed
Test duration	96 h
Procedure	Artificial irradiation.

# PABA BU/15 CUS - Cable marker



0824441

<https://www.phoenixcontact.com/us/products/0824441>

## Temperature resistance

Specification	ANSI/UL 969-2018:03 (following)
Test duration	240 h
Rating 125 °C (150 °C)	Test passed

## Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03 DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropanol (99%) [67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed
Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2]	Test passed
Ethanol (99 %) [CAS No. 64-17-5]	Test passed

## Immersion in chemicals, oil & fuel

Specification	ISO 175:2010 (following)
Test duration	168 h
Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2]	Test passed
Saltwater (saturated 350 g/l) [CAS No. - ]	Test passed
Ethanol (99 %) [CAS No. 64-17-5]	Test passed
Diesel [CAS No. 68476-34-6]	Test passed
IRM 901	Test passed
IRM 902	Test passed
IRM 903	Test passed

## Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	DIN 50018:2013-05
Result	Test passed
Climate level	AHT 1.0 S
Cycles	2

## Salt spray test

Specification	DIN EN 60068-2-11:2000-02
Result	Test passed
Test duration	96 h

## Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

## Mounting

# PABA BU/15 CUS - Cable marker



0824441

<https://www.phoenixcontact.com/us/products/0824441>

Mounting type	thread on
---------------	-----------

# PABA BU/15 CUS - Cable marker



0824441

<https://www.phoenixcontact.com/us/products/0824441>

## Classifications

### ECLASS

ECLASS-13.0

27281102

### ETIM

ETIM 9.0

EC001530

### UNSPSC

UNSPSC 21.0

39131500

# PABA BU/15 CUS - Cable marker



0824441

<https://www.phoenixcontact.com/us/products/0824441>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### EU REACH SVHC

REACH candidate substance (CAS No.)	Perfluorobutane sulfonic acid (PFBS) and its salts(CAS: n/a)
SCIP	10acf996-c740-4b93-ac7c-8a14750ed9a7

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)