

TMT 100 R CUS - Marker for terminal blocks



0824501

<https://www.phoenixcontact.com/us/products/0824501>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Marker for terminal blocks, Roll, can be ordered: by line, white (RAL 9010), labeled according to customer specifications, unperforated, mounting type: latching, for terminal block width: 101.5 mm, Number of individual labels: 1000, text field height: 101.5 mm, text field width: 6.35 mm

Your advantages

- Labeling service: Phoenix Contact can custom-label all TMT ... markers in accordance with your requirements
- The TMT labeling range includes markers for all products with tall and flat marker grooves

Commercial data

Item number	0824501
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	BG8111
GTIN	4046356355971
Weight per piece (including packing)	1.99 g
Weight per piece (excluding packing)	1.99 g
Country of origin	PL

TMT 100 R CUS - Marker for terminal blocks



0824501

<https://www.phoenixcontact.com/us/products/0824501>

Technical data

Product properties

Product type	Terminal marker
Pitch	101.5 mm

Marking

Number of individual labels	1000
Number of individual labels per row	1
Slot type	flat
Identification technology	Thermal transfer

Dimensions

Width	100.00 mm
Height	6.35 mm
Depth	0.17 mm
Pitch	101.5 mm
Length	6.35 mm

Text field

Text field width	6.35 mm
Text field height	101.5 mm

Material specifications

Foil strength	175 µm
Color	white (RAL 9010)
Base element material	Polyester
Components	free from silicone and halogen

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 150 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)

Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VDMA 24364-A1-L:2018-05
Result	Test passed

Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VW PV 3.10.7:2005-02
Result	Test passed

TMT 100 R CUS - Marker for terminal blocks



0824501

<https://www.phoenixcontact.com/us/products/0824501>

Scratch resistance

Specification	EN ISO 1518-1:2023 (following)
Requirements	≥ 5 N
Result	Test passed

Tesafilm test

Specification	DIN EN ISO 2409:2020-12 (following)
Result	Test passed

UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
Result	Test passed
Test duration	96 h
Procedure	Artificial irradiation.

Temperature storage

Specification	IEC 60068-2-2:2007-07
Result	Test passed
Procedure	Test Bb
Duration	96 h
Temperature for testing	120 °C

Temperature resistance

Specification	ANSI/UL 969-2018:03 (following)
Test duration	240 h
Rating 150 °C (180 °C)	Test passed

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03 DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropanol (99%) [67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed
Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2]	Test passed
Ethanol (99 %) [CAS No. 64-17-5]	Test passed

Immersion in chemicals, oil & fuel

Specification	ISO 175:2010 (following)
Test duration	168 h
Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2]	Test passed
Saltwater (saturated 350 g/l) [CAS No. -]	Test passed

TMT 100 R CUS - Marker for terminal blocks



0824501

<https://www.phoenixcontact.com/us/products/0824501>

Ethanol (99 %) [CAS No. 64-17-5]	Test passed
Gasoline [CAS No. 64742-49-0]	Test passed
Diesel [CAS No. 68476-34-6]	Test passed
IRM 901	Test passed
IRM 902	Test passed
IRM 903	Test passed

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	EN ISO 22479:2022-06
Result	Test passed
Procedure	Method B
Cycles	2

Salt spray test

Specification	DIN EN IEC 60068-2-11 (VDE 0468-2-11):2022-10
Result	Test passed
Test duration	96 h

Mounting

Mounting type	latching
---------------	----------

TMT 100 R CUS - Marker for terminal blocks

0824501

<https://www.phoenixcontact.com/us/products/0824501>

Drawings

Schematic diagram



- ① Horizontal
- ② Vertical

TMT 100 R CUS - Marker for terminal blocks



0824501

<https://www.phoenixcontact.com/us/products/0824501>

Classifications

ECLASS

ECLASS-13.0	27281101
ECLASS-15.0	27281101

ETIM

ETIM 10.0	EC000761
-----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

TMT 100 R CUS - Marker for terminal blocks



0824501

<https://www.phoenixcontact.com/us/products/0824501>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com