

# UC-EMLP (11X9) CUS - Plastic label



0824547

<https://www.phoenixcontact.com/us/products/0824547>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Plastic label, can be ordered: by sheet, white (RAL 9010), labeled according to customer specifications, mounting type: adhesive, text field height: 9 mm, text field width: 11 mm



## Your advantages

- All UC-EMLP ... self-adhesive device markers can also be supplied labeled according to customer requirements
- The wide temperature range means that the labels can be used in control cabinets as well as the field
- Self-adhesive with good adhesive properties

## Commercial data

|                                      |                                |
|--------------------------------------|--------------------------------|
| Item number                          | 0824547                        |
| Packing unit                         | 1 pc                           |
| Minimum order quantity               | 1 pc                           |
| Note                                 | Made to order (non-returnable) |
| Sales key                            | BG24                           |
| Product key                          | BG8147                         |
| GTIN                                 | 4046356356633                  |
| Weight per piece (including packing) | 6.75 g                         |
| Weight per piece (excluding packing) | 6.75 g                         |
| Customs tariff number                | 49119900                       |
| Country of origin                    | PL                             |

## Technical data

### Product properties

|              |               |
|--------------|---------------|
| Product type | Device marker |
|--------------|---------------|

### Marking

|                                     |                   |
|-------------------------------------|-------------------|
| Number of individual labels per row | 2                 |
| Identification technology           | UV LED technology |

### Dimensions

|        |          |
|--------|----------|
| Width  | 11.00 mm |
| Height | 9.00 mm  |
| Depth  | 1.30 mm  |
| Length | 9 mm     |

### Text field

|                   |       |
|-------------------|-------|
| Text field width  | 11 mm |
| Text field height | 9 mm  |

### Material specifications

|  |                                |
|--|--------------------------------|
| Adhesive strength                                      | 250 µm                         |
| Adhesive   | Acrylic                        |
| Color  | white (RAL 9010)               |
| Material   | PA                             |
| Flammability rating according to UL 94                 | V2                             |
| Base element material                                  | PA                             |
| Fire protection for rail vehicles (DIN EN 45545-2) R22 | HL 1 - HL 2                    |
| Fire protection for rail vehicles (DIN EN 45545-2) R23 | HL 1 - HL 2                    |
| Fire protection for rail vehicles (DIN EN 45545-2) R24 | HL 1 - HL 2                    |
| Components   | free from silicone and halogen |

### Environmental and real-life conditions

#### Ambient conditions

|   |   |
|---|---|
| Ambient temperature (operation)                     | -40 °C ... 120 °C   |
| Recommended ambient temperature (storage/transport) | 23 °C   |
| Recommended humidity (storage/transport)            | 50 % (Storage in a dry and dark place in the original packaging is recommended) |

#### Test for substances that would hinder coating with paint or varnish

|   |                         |
|---|-------------------------|
| Testing for paint wetting impairment substances (LABS-conformity) | VDMA 24364-A1-L:2018-05 |
| Result  | Test passed             |

#### Test for substances that would hinder coating with paint or varnish

|   |                      |
|---|----------------------|
| Testing for paint wetting impairment substances (LABS-conformity) | VW PV 3.10.7:2005-02 |
|---|----------------------|

# UC-EMLP (11X9) CUS - Plastic label



0824547

<https://www.phoenixcontact.com/us/products/0824547>

|        |             |
|--------|-------------|
| Result | Test passed |
|--------|-------------|

## Scratch resistance

|               |                                |
|---------------|--------------------------------|
| Specification | EN ISO 1518-1:2023 (following) |
| Requirements  | ≥ 5 N                          |
| Result        | Test passed                    |

## Tesafilm test

|               |                                     |
|---------------|-------------------------------------|
| Specification | DIN EN ISO 2409:2020-12 (following) |
| Result        | Test passed                         |

## UV resistance

|               |                                       |
|---------------|---------------------------------------|
| Specification | DIN EN ISO 4892-2:2021-11 (following) |
| Result        | Test passed                           |
| Test duration | 96 h                                  |
| Procedure     | Artificial irradiation.               |

## Weathering-resistance

|               |                           |
|---------------|---------------------------|
| Specification | DIN EN ISO 4892-2:2021-11 |
| Result        | Test passed               |
| Test duration | 1000 h                    |
| Procedure     | A                         |

## Temperature resistance

|                        |                                 |
|------------------------|---------------------------------|
| Specification          | ANSI/UL 969-2018:03 (following) |
| Test duration          | 240 h                           |
| Rating 125 °C (150 °C) | Test passed                     |

## Wipe resistance of inscriptions

|   |  |
|---|--|
| Specification                                     | DIN EN 61010-1 (VDE 0411-01):2020-03<br>DIN EN 62208 (VDE 0660-511):2012-06 (in parts) |
| Isopropanol (99%) [67-63-0]                       | Test passed  |
| n-Hexane<br>[CAS No. 110-54-3]                    | Test passed  |
| Water + Petroleum ether<br>[CAS No. 64742-82-1]   | Test passed  |
| Sodium hydroxide 0.1 mol/l<br>[CAS No. 1310-73-2] | Test passed  |
| Ethanol (99 %)<br>[CAS No. 64-17-5]               | Test passed  |
| Acetone (99 %)<br>[CAS No. 67-64-1]               | Test passed  |

## Immersion in chemicals, oil & fuel

|   |                          |
|---|--------------------------|
| Specification                                 | ISO 175:2010 (following) |
| Test duration                                 | 168 h                    |
| Saltwater (saturated 350 g/l)<br>[CAS No. - ] | Test passed              |

# UC-EMLP (11X9) CUS - Plastic label



0824547

<https://www.phoenixcontact.com/us/products/0824547>

|                                |             |
|--------------------------------|-------------|
| Diesel<br>[CAS No. 68476-34-6] | Test passed |
| IRM 901                        | Test passed |
| IRM 902                        | Test passed |
| IRM 903                        | Test passed |

## Testing in a condensation changing climate in the presence of sulfur dioxide

|               |                      |
|---------------|----------------------|
| Specification | EN ISO 22479:2022-06 |
| Result        | Test passed          |
| Procedure     | Method B             |
| Cycles        | 2                    |

## Salt spray test

|               |   |
|---------------|---|
| Specification | DIN EN IEC 60068-2-11 (VDE 0468-2-11):2022-10 |
| Result        | Test passed                                   |
| Test duration | 96 h  |

## Standards and regulations

|                 |                             |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|-----------------|-----------------------------|

## Standards

|                       |            |
|-----------------------|------------|
| Standards/regulations | EN 45545-2 |
|-----------------------|------------|

## Mounting

|               |          |
|---------------|----------|
| Mounting type | adhesive |
|---------------|----------|

# UC-EMLP (11X9) CUS - Plastic label



0824547

<https://www.phoenixcontact.com/us/products/0824547>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27281103 |
| ECLASS-15.0 | 27281103 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC001288 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39131500 |
|-------------|----------|

# UC-EMLP (11X9) CUS - Plastic label



0824547

<https://www.phoenixcontact.com/us/products/0824547>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

### EF3.1 Climate Change

|         |               |
|---------|---------------|
| CO2e kg | 0.138 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)