

LBHZ 2/WH CUS - Cable marker



0824439

<https://www.phoenixcontact.com/us/products/0824439>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable marker, can be ordered: Strip, white (RAL 9010), labeled according to customer specifications, cable diameter range: 1.5 ... 3.2 mm, mounting type: slide-on, Number of individual labels: 10, text field height: 10 mm, text field width: 4.5 mm

Commercial data

Item number	0824439
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	BG8122
GTIN	4046356353076
Weight per piece (including packing)	1.26 g
Weight per piece (excluding packing)	0.54 g
Country of origin	PL

LBHZ 2/WH CUS - Cable marker



0824439

<https://www.phoenixcontact.com/us/products/0824439>

Technical data

Product properties

Product type	Conductor marker
--------------	------------------

Marking

Number of individual labels	10
Number of individual labels per row	10
Slot type	Card form
Identification technology	Plotter

Dimensions

Width	4.70 mm
Height	10.50 mm
Depth	5.70 mm
Length	10 mm

Text field

Text field width	4.5 mm
Text field height	10 mm

Material specifications

Color	white (RAL 9010)
Material	PA
Flammability rating according to UL 94	V2
Base element material	PA
Components	free from silicone and halogen

Cable/line

External cable diameter	1.5 mm ... 3.2 mm
-------------------------	-------------------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)

UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
---------------	---------------------------------------

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-1):2011-07
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)

Standards and regulations

LBHZ 2/WH CUS - Cable marker



0824439

<https://www.phoenixcontact.com/us/products/0824439>

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Mounting

Mounting type	slide-on
---------------	----------

LBHZ 2/WH CUS - Cable marker



0824439

<https://www.phoenixcontact.com/us/products/0824439>

Classifications

ECLASS

ECLASS-13.0	27281102
ECLASS-15.0	27281102

ETIM

ETIM 10.0	EC001530
-----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

LBHZ 2/WH CUS - Cable marker



0824439

<https://www.phoenixcontact.com/us/products/0824439>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
-----------------------------------------	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com