

# SK U/5,0 WH CUS - Marker strip



0824465

<https://www.phoenixcontact.com/us/products/0824465>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Marker strip, Sheet, can be ordered: in sheets, white (RAL 9010), labeled according to customer specifications, mounting type: adhesive, Number of individual labels: 630, text field height: 5 mm, text field width: 186 mm



## Commercial data

|                                      |                                |
|--------------------------------------|--------------------------------|
| Item number                          | 0824465                        |
| Packing unit                         | 1 pc                           |
| Minimum order quantity               | 1 pc                           |
| Note                                 | Made to order (non-returnable) |
| Product key                          | BG8114                         |
| GTIN                                 | 4046356354974                  |
| Weight per piece (including packing) | 10 g                           |
| Weight per piece (excluding packing) | 9 g                            |
| Country of origin                    | PL                             |

# SK U/5,0 WH CUS - Marker strip



0824465

<https://www.phoenixcontact.com/us/products/0824465>

## Technical data

### Product properties

|              |                 |
|--------------|-----------------|
| Product type | Terminal marker |
|--------------|-----------------|

### Marking

|                                     |                       |
|-------------------------------------|-----------------------|
| Number of individual labels         | 630                   |
| Number of individual labels per row | 18                    |
| Number of marker strips             | 35                    |
| Slot type                           | flat                  |
| Identification technology           | Office laser printing |

### Dimensions

|        |           |
|--------|-----------|
| Width  | 186.00 mm |
| Height | 5.00 mm   |
| Depth  | 0.07 mm   |
| Length | 186 mm    |

### Text field

|                   |        |
|-------------------|--------|
| Text field width  | 186 mm |
| Text field height | 5 mm   |

### Material specifications

|                       |                                |
|-----------------------|--------------------------------|
| Foil strength         | 50 µm                          |
| Adhesive strength     | 20 µm                          |
| Adhesive              | Acrylic                        |
| Color                 | white (RAL 9010)               |
| Material              | Polyester                      |
| Base element material | Polyester                      |
| Components            | free from silicone and halogen |

### Environmental and real-life conditions

#### Ambient conditions

|   |                   |
|---|-------------------|
| Ambient temperature (operation)                     | -40 °C ... 150 °C |
| Recommended ambient temperature (storage/transport) | 20 °C             |
| Recommended humidity (storage/transport)            | 40 % ... 50 %     |

#### Test for substances that would hinder coating with paint or varnish

|   |                    |
|---|--------------------|
| Testing for paint wetting impairment substances (LABS-conformity) | VDMA 24364:2018-05 |
| Result  | Test passed        |

#### Scratch resistance

|               |                                |
|---------------|--------------------------------|
| Specification | EN ISO 1518-1:2023 (following) |
| Requirements  | ≥ 5 N                          |

# SK U/5,0 WH CUS - Marker strip



0824465

<https://www.phoenixcontact.com/us/products/0824465>

|        |             |
|--------|-------------|
| Result | Test passed |
|--------|-------------|

## Tesafilem test

|               |                                     |
|---------------|-------------------------------------|
| Specification | DIN EN ISO 2409:2020-12 (following) |
| Result        | Test passed                         |

## UV resistance

|               |                                       |
|---------------|---------------------------------------|
| Specification | DIN EN ISO 4892-2:2021-11 (following) |
| Result        | Test passed                           |
| Test duration | 96 h                                  |
| Procedure     | Artificial irradiation.               |

## Temperature resistance

|                        |                                 |
|------------------------|---------------------------------|
| Specification          | ANSI/UL 969-2018:03 (following) |
| Test duration          | 240 h                           |
| Rating 200 °C (230 °C) | Test passed                     |

## Wipe resistance of inscriptions

|   |  |
|---|--|
| Specification                                     | DIN EN 61010-1 (VDE 0411-01):2020-03<br>DIN EN 62208 (VDE 0660-511):2012-06 (in parts) |
| Isopropanol (99%) [67-63-0]                       | Test passed  |
| n-Hexane<br>[CAS No. 110-54-3]                    | Test passed  |
| Water + Petroleum ether<br>[CAS No. 64742-82-1]   | Test passed  |
| Sodium hydroxide 0.1 mol/l<br>[CAS No. 1310-73-2] | Test passed  |
| Ethanol (99 %)<br>[CAS No. 64-17-5]               | Test passed  |

## Immersion in chemicals, oil & fuel

|   |                          |
|---|--------------------------|
| Specification                                 | ISO 175:2010 (following) |
| Test duration                                 | 168 h                    |
| Saltwater (saturated 350 g/l)<br>[CAS No. - ] | Test passed              |
| Diesel<br>[CAS No. 68476-34-6]                | Test passed              |
| IRM 901                                       | Test passed              |
| IRM 902                                       | Test passed              |
| IRM 903                                       | Test passed              |

## Testing in a condensation changing climate in the presence of sulfur dioxide

|               |                          |
|---------------|--------------------------|
| Specification | DIN EN ISO 22479:2022-08 |
| Result        | Test passed              |
| Procedure     | Method B                 |
| Cycles        | 2                        |

## Salt spray test

|               |   |
|---------------|---|
| Specification | DIN EN IEC 60068-2-11 (VDE 0468-2-11):2022-10 |
|---------------|---|

# SK U/5,0 WH CUS - Marker strip



0824465

<https://www.phoenixcontact.com/us/products/0824465>

|               |             |
|---------------|-------------|
| Result        | Test passed |
| Test duration | 96 h        |

## Standards and regulations

|                 |                             |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|-----------------|-----------------------------|

## Mounting

|               |          |
|---------------|----------|
| Mounting type | adhesive |
|---------------|----------|

# SK U/5,0 WH CUS - Marker strip

0824465

<https://www.phoenixcontact.com/us/products/0824465>



## Drawings

Schematic diagram



- ① Horizontal
- ② Vertical

# SK U/5,0 WH CUS - Marker strip



0824465

<https://www.phoenixcontact.com/us/products/0824465>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27281101 |
| ECLASS-15.0 | 27281101 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC000761 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39131500 |
|-------------|----------|

# SK U/5,0 WH CUS - Marker strip



0824465

<https://www.phoenixcontact.com/us/products/0824465>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)