SS-3R 20X7 WH CUS - Contactor marker

0824467

https://www.phoenixcontact.com/us/products/0824467

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Contactor marker, can be ordered: by sheet, white (RAL 9010), labeled according to customer specifications, mounting type: snapped into marker carrier, for terminal block width: 20 mm, text field height: 7 mm, text field width: 20 mm

Commercial data

Item number	0824467
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	BG8143
GTIN	4046356355186
Weight per piece (including packing)	5 g
Weight per piece (excluding packing)	4.6 g
Country of origin	PL

Technical data

Product properties

Product type	Device marker
Pitch	20 mm

Marking

Marking groove	high
Identification technology	Plotter

Dimensions

Width	19.00 mm
Height	7.50 mm
Depth	1.00 mm
Pitch	20 mm
Length	20 mm

Text field

Text field width	20 mm
Text field height	7 mm

Material specifications

Color	white (RAL 9010)
Material	ABS
Flammability rating according to UL 94	V0
Base element material	ABS

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 80 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)

UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)

Standards and regulations

Wipe resistance	DIN 30646
	DIN VDE 0611-1

Mounting

Mounting type	snapped into marker carrier

Classifications

ECLASS

ECLASS-13.0	27281103
ECLASS-15.0	27281103

ETIM

ETIM 10.0	EC001288

UNSPSC

UNSPSC 21.0	39131500

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com