

TML (101X4,2)R TR CUS - Marker strip



0824472

<https://www.phoenixcontact.com/us/products/0824472>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Marker strip, Roll, can be ordered: by line, labeled according to customer specifications, can be labeled with: THERMOMARK ROLL 2.0, THERMOMARK ROLL, THERMOMARK ROLL X1, THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, mounting type: adhesive, for terminal block width: 101 mm, Number of individual labels: 1, text field height: 4.2 mm, text field width: 101 mm

Your advantages

- The self-adhesive marker strips from the SK marking range mark products without a marker groove, ideal for marking COMBICON connectors
- The TML labeling range offers the option of subsequent labeling of zack marker strip and flat zack marker strip materials using a marking foil
- Labeling service: Phoenix Contact can custom-label all TML ... markers in accordance with your requirements

Commercial data

Item number	0824472
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	BG8111
GTIN	4046356355230
Weight per piece (including packing)	0.147 g
Weight per piece (excluding packing)	0.147 g
Country of origin	PL

TML (101X4,2)R TR CUS - Marker strip



0824472

<https://www.phoenixcontact.com/us/products/0824472>

Technical data

Product properties

Product type	Terminal marker
Pitch	101 mm

Marking

Number of individual labels	1
Number of individual labels per row	1
Slot type	flat
Identification technology	Thermotransfer

Dimensions

Width	101.00 mm
Height	4.20 mm
Depth	0.10 mm
Pitch	101 mm
Length	101 mm

Text field

Text field width	101 mm
Text field height	4.2 mm

Material specifications

RoHS compliant	yes
Foil strength	23 µm
Adhesive strength	20 µm
Adhesive	Acrylic
Color	transparent
Material	Polyester
Base element material	Polyester
Components	Silicone-free

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 150 °C
Recommended ambient temperature (storage/transport)	10 °C
Recommended humidity (storage/transport)	35 % ... 65 %

Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VW PV 3.10.7:2005-02
Result	Test passed

UV resistance

TML (101X4,2)R TR CUS - Marker strip



0824472

<https://www.phoenixcontact.com/us/products/0824472>

Specification	DIN EN ISO 4892-2:2021-11 (following)
Result	Test passed
Test duration	96 h

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Mounting

Mounting type	adhesive
---------------	----------

TML (101X4,2)R TR CUS - Marker strip

0824472

<https://www.phoenixcontact.com/us/products/0824472>

Drawings

Schematic diagram



- ① Horizontal
- ② Vertical

TML (101X4,2)R TR CUS - Marker strip



0824472

<https://www.phoenixcontact.com/us/products/0824472>

Classifications

ECLASS

ECLASS-13.0	27281101
ECLASS-15.0	27281101

ETIM

ETIM 10.0	EC000761
-----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

TML (101X4,2)R TR CUS - Marker strip



0824472

<https://www.phoenixcontact.com/us/products/0824472>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com