

ZBFM 5 CUS - Flat zack marker sheet



0825037

<https://www.phoenixcontact.com/us/products/0825037>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Flat zack marker sheet, can be ordered: by sheet, white (RAL 9010), labeled according to customer specifications, mounting type: snap into flat marker groove, for terminal block width: 5.2 mm, Number of individual labels: 120, text field height: 4.5 mm, text field width: 5 mm



Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 0825037 |
| Packing unit | 1 pc |
| Minimum order quantity | 50 pc |
| Note | Made to order (non-returnable) |
| Sales key | BG24 |
| Product key | BG8113 |
| GTIN | 4046356357685 |
| Weight per piece (including packing) | 5.205 g |
| Weight per piece (excluding packing) | 5.205 g |
| Customs tariff number | 49119900 |
| Country of origin | DE |

ZBFM 5 CUS - Flat zack marker sheet



0825037

<https://www.phoenixcontact.com/us/products/0825037>

Technical data

Product properties

| | |
|--------------|-----------------|
| Product type | Terminal marker |
| Pitch | 5.2 mm |

Marking

| | |
|-------------------------------------|------|
| Number of individual labels | 120 |
| Number of individual labels per row | 12 |
| Slot type | flat |

Dimensions

| | |
|--------|---------|
| Width | 4.55 mm |
| Height | 6.50 mm |
| Depth | 1.60 mm |
| Pitch | 5.2 mm |

Text field

| | |
|-------------------|--------|
| Text field width | 5 mm |
| Text field height | 4.5 mm |

Material specifications

| | |
|--|--------------------------------|
| Color | white (RAL 9010) |
| Material | PA |
| Flammability rating according to UL 94 | V2 |
| Base element material | PA |
| Components | free from silicone and halogen |

Environmental and real-life conditions

Ambient conditions

| | |
|---|---|
| Ambient temperature (operation) | -40 °C ... 100 °C |
| Recommended ambient temperature (storage/transport) | 23 °C |
| Recommended humidity (storage/transport) | 50 % (Storage in a dry and dark place in the original packaging is recommended) |

UV resistance

| | |
|---------------|---------------------------------------|
| Specification | DIN EN ISO 4892-2:2021-11 (following) |
|---------------|---------------------------------------|

Wipe resistance of inscriptions

| | |
|---------------|--|
| Specification | DIN EN 61010-1 (VDE 0411-01):2020-03 |
| | DIN EN 62208 (VDE 0660-511):2012-06 (in parts) |

Standards and regulations

| | |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|-----------------|-----------------------------|

Mounting

ZBFM 5 CUS - Flat zack marker sheet



0825037

<https://www.phoenixcontact.com/us/products/0825037>

| | |
|---------------|------------------------------|
| Mounting type | snap into flat marker groove |
|---------------|------------------------------|

ZBFM 5 CUS - Flat zack marker sheet



0825037

<https://www.phoenixcontact.com/us/products/0825037>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27281101 |
| ECLASS-15.0 | 27281101 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC000761 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39131500 |
|-------------|----------|

ZBFM 5 CUS - Flat zack marker sheet



0825037

<https://www.phoenixcontact.com/us/products/0825037>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com