

# SK 2,8 REEL P3,5 WH CUS - Marker card



0825121

<https://www.phoenixcontact.com/us/products/0825121>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Marker card, Roll, can be ordered: by card, white (RAL 9010), labeled according to customer specifications, mounting type: adhesive, for terminal block width: 3.5 mm, Number of individual labels: 14

## Your advantages

- Labeling service: Phoenix Contact can custom-label all SK ... markers in accordance with your requirements
- Ideal for labeling COMBICON connectors
- The SK labeling range offers self-adhesive marker strips for labeling products that do not have a marker groove

## Commercial data

Item number	0825121
Packing unit	1 pc
Minimum order quantity	50 pc
Note	Made to order (non-returnable)
Sales key	BG24
Product key	BG8113
GTIN	4046356355049
Weight per piece (including packing)	0.758 g
Weight per piece (excluding packing)	0.25 g
Customs tariff number	49119900
Country of origin	DE

# SK 2,8 REEL P3,5 WH CUS - Marker card



0825121

<https://www.phoenixcontact.com/us/products/0825121>

## Technical data

### Notes

Order information:	Marking up to max. 25-pos.
--------------------	----------------------------

### Product properties

Product type	Terminal marker
Pitch	3.5 mm

### Marking

Number of individual labels	14
Number of individual labels per row	1
Number of marker strips	14
Slot type	Label
Identification technology	Thermal transfer

### Dimensions

Width	50.00 mm
Height	2.80 mm
Depth	0.07 mm
Pitch	3.5 mm

### Material specifications

Foil strength	53 µm
Adhesive strength	20 µm
Adhesive	Acrylic
Color	white (RAL 9010)
Material	Polyester
Base element material	Polyester
Components	free from silicone and halogen

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 150 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %

#### Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VW PV 3.10.7:2005-02
Result	Test passed

#### UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
Result	Test passed

# SK 2,8 REEL P3,5 WH CUS - Marker card



0825121

<https://www.phoenixcontact.com/us/products/0825121>

Test duration	96 h
---------------	------

## Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)

## Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

## Mounting

Mounting type	adhesive
---------------	----------

# SK 2,8 REEL P3,5 WH CUS - Marker card

0825121

<https://www.phoenixcontact.com/us/products/0825121>

## Drawings

Schematic diagram



- ① Horizontal
- ② Vertical

# SK 2,8 REEL P3,5 WH CUS - Marker card



0825121

<https://www.phoenixcontact.com/us/products/0825121>

## Classifications

### ECLASS

ECLASS-13.0	27281101
ECLASS-15.0	27281101

### ETIM

ETIM 10.0	EC000761
-----------	----------

### UNSPSC

UNSPSC 21.0	39131500
-------------	----------

# SK 2,8 REEL P3,5 WH CUS - Marker card



0825121

<https://www.phoenixcontact.com/us/products/0825121>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)