

SK 5,0 REEL P10 WH CUS - Marker card



0825129

<https://www.phoenixcontact.com/us/products/0825129>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Marker card, Roll, can be ordered: by card, white (RAL 9010), labeled according to customer specifications, mounting type: adhesive, for terminal block width: 10 mm, Number of individual labels: 10

Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 0825129 |
| Packing unit | 1 pc |
| Minimum order quantity | 50 pc |
| Note | Made to order (non-returnable) |
| Sales key | BG24 |
| Product key | BG8113 |
| GTIN | 4046356355100 |
| Weight per piece (including packing) | 1.97 g |
| Weight per piece (excluding packing) | 0.6 g |
| Customs tariff number | 49119900 |
| Country of origin | DE |

SK 5,0 REEL P10 WH CUS - Marker card



0825129

<https://www.phoenixcontact.com/us/products/0825129>

Technical data

Notes

| | |
|--------------------|----------------------------|
| Order information: | Marking up to max. 25-pos. |
|--------------------|----------------------------|

Product properties

| | |
|--------------|-----------------|
| Product type | Terminal marker |
| Pitch | 10 mm |

Marking

| | |
|-------------------------------------|------------------|
| Number of individual labels | 10 |
| Number of individual labels per row | 1 |
| Number of marker strips | 10 |
| Slot type | Label |
| Identification technology | Thermal transfer |

Dimensions

| | |
|--------|----------|
| Width | 50.00 mm |
| Height | 5.00 mm |
| Depth | 0.10 mm |
| Pitch | 10 mm |

Material specifications

| | |
|-----------------------|--------------------------------|
| Foil strength | 53 µm |
| Adhesive strength | 20 µm |
| Adhesive | Acrylic |
| Color | white (RAL 9010) |
| Material | Polyester |
| Base element material | Polyester |
| Components | free from silicone and halogen |

Environmental and real-life conditions

Ambient conditions

| | |
|---|---|
| Ambient temperature (operation) | -40 °C ... 150 °C |
| Recommended ambient temperature (storage/transport) | 23 °C |
| Recommended humidity (storage/transport) | 50 % (Storage in a dry and dark place in the original packaging is recommended) |

Test for substances that would hinder coating with paint or varnish

| | |
|---|----------------------|
| Testing for paint wetting impairment substances (LABS-conformity) | VW PV 3.10.7:2005-02 |
| Result | Test passed |

UV resistance

| | |
|---------------|---------------------------------------|
| Specification | DIN EN ISO 4892-2:2021-11 (following) |
|---------------|---------------------------------------|

SK 5,0 REEL P10 WH CUS - Marker card



0825129

<https://www.phoenixcontact.com/us/products/0825129>

| | |
|---------------|-------------|
| Result | Test passed |
| Test duration | 96 h |

Wipe resistance of inscriptions

| | |
|---------------|--|
| Specification | DIN EN 61010-1 (VDE 0411-01):2020-03 |
| | DIN EN 62208 (VDE 0660-511):2012-06 (in parts) |

Standards and regulations

| | |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|-----------------|-----------------------------|

Mounting

| | |
|---------------|----------|
| Mounting type | adhesive |
|---------------|----------|

SK 5,0 REEL P10 WH CUS - Marker card

0825129

<https://www.phoenixcontact.com/us/products/0825129>

Drawings

Schematic diagram



- ① Horizontal
- ② Vertical

SK 5,0 REEL P10 WH CUS - Marker card



0825129

<https://www.phoenixcontact.com/us/products/0825129>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27281101 |
| ECLASS-15.0 | 27281101 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC000761 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39131500 |
|-------------|----------|

SK 5,0 REEL P10 WH CUS - Marker card



0825129

<https://www.phoenixcontact.com/us/products/0825129>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com