

SD-WMTBS (NU) CC - Wire marking tag



0826527

<https://www.phoenixcontact.com/us/products/0826527>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Wire marking tag, Mixed color, horizontal: Numbers, mounting type: slide-on, cable diameter: > 16 mm, text field height: 2.6 mm, text field width: 4.3 mm

The figure shows the version SD-WMTBS (S) YE

Your advantages

- The printed individual markers are pushed onto the corresponding holders
- Cable markers for marking cables and conductors with larger cross sections

Commercial data

Item number	0826527
Packing unit	100 pc
Minimum order quantity	100 pc
Sales key	NULL
Product key	BG2322
Weight per piece (including packing)	333 g
Weight per piece (excluding packing)	333 g
Customs tariff number	39269097
Country of origin	SE

SD-WMTBS (NU) CC - Wire marking tag



0826527

<https://www.phoenixcontact.com/us/products/0826527>

Technical data

Notes

General	Please specify the required marking with order: Minimum order per imprint: 1 packing unit
---------	---

Product properties

Product type	Conductor marker
--------------	------------------

Marking

Printing direction	horizontal
Printing	Numbers

Dimensions

Width	4.3 mm
Length	11.3 mm

Text field

Text field width	4.3 mm
Text field height	2.6 mm

Material specifications

Color	multicolored (RAL -)
Flammability rating according to UL 94	V2
Base element material	PVC
Components	Free from silicone and cadmium

Cable/line

External cable diameter	> 16.00 mm
-------------------------	------------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-30 °C ... 60 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)

Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VW PV 3.10.7:2005-02
Result	Test passed

UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
Result	Test passed
Test duration	96 h

SD-WMTBS (NU) CC - Wire marking tag



0826527

<https://www.phoenixcontact.com/us/products/0826527>

Procedure	Artificial irradiation.
-----------	-------------------------

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-1):2011-07
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropanol (99%) [67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	DIN EN ISO 22479:2022-08
Result	Test passed
Procedure	Method B
Cycles	2

Salt spray test

Specification	DIN EN IEC 60068-2-11 (VDE 0468-2-11):2022-10
Result	Test passed
Test duration	96 h

Mounting

Mounting type	slide-on
---------------	----------

SD-WMTBS (NU) CC - Wire marking tag



0826527

<https://www.phoenixcontact.com/us/products/0826527>

Classifications

ECLASS

ECLASS-13.0	27281102
ECLASS-15.0	27281102

ETIM

ETIM 10.0	EC001530
-----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

SD-WMTBS (NU) CC - Wire marking tag



0826527
<https://www.phoenixcontact.com/us/products/0826527>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com