

SD-WMTBS (NEUTRAL) CC - Wire marking tag



0826637

<https://www.phoenixcontact.com/us/products/0826637>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Wire marking tag, yellow (RAL 1018): without print, mounting type: slide-on, cable diameter: > 16 mm, text field height: 2.6 mm, text field width: 4.3 mm

The figure shows the version SD-WMTBS (S) YE

Your advantages

- The printed individual markers are pushed onto the corresponding holders
- Cable markers for marking cables and conductors with larger cross sections

Commercial data

Item number	0826637
Packing unit	100 pc
Minimum order quantity	100 pc
Product key	BG2312
GTIN	4046356414494
Weight per piece (including packing)	0.157 g
Weight per piece (excluding packing)	0.143 g
Country of origin	SE

Technical data

Product properties

Product type	Conductor marker
--------------	------------------

Marking

Printing	without print
----------	---------------

Dimensions

Width	4.3 mm
Length	11.3 mm

Text field

Text field width	4.3 mm
Text field height	2.6 mm

Material specifications

Color	yellow (RAL 1018)
Material	PVC
Flammability rating according to UL 94	V2
Base element material	PVC
Components	Free from silicone and cadmium

Cable/line

External cable diameter	> 16.00 mm
-------------------------	------------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-30 °C ... 60 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)

Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VW PV 3.10.7:2005-02
Result	Test passed

UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
Result	Test passed
Test duration	96 h

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-1):2011-07
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)

SD-WMTBS (NEUTRAL) CC - Wire marking tag



0826637

<https://www.phoenixcontact.com/us/products/0826637>

Isopropanol (99%) [67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	DIN EN ISO 22479:2022-08
Result	Test passed
Procedure	Method B
Cycles	2

Salt spray test

Specification	DIN EN IEC 60068-2-11 (VDE 0468-2-11):2022-10
Result	Test passed
Test duration	96 h

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Mounting

Mounting type	slide-on
---------------	----------

SD-WMTBS (NEUTRAL) CC - Wire marking tag



0826637

<https://www.phoenixcontact.com/us/products/0826637>

Classifications

ECLASS

ECLASS-13.0	27281102
ECLASS-15.0	27281102

ETIM

ETIM 10.0	EC001530
-----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

SD-WMTBS (NEUTRAL) CC - Wire marking tag



0826637

<https://www.phoenixcontact.com/us/products/0826637>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com