

SD-WMS 10 (CH)R YE:M - Wire marking tag



0826255:M

<https://www.phoenixcontact.com/us/products/0826255:M>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Wire marking tag, labeled with the capital letter: M, lettering field size: 6.6 x 4.3 mm, yellow, mounting type: thread on

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 0826255:M |
| Packing unit | 250 pc |
| Minimum order quantity | 250 pc |
| Product key | BG2221 |
| GTIN | 4046356425537 |
| Weight per piece (including packing) | 0.24 g |
| Weight per piece (excluding packing) | 0.156 g |
| Country of origin | SE |

SD-WMS 10 (CH)R YE:M - Wire marking tag



0826255:M

<https://www.phoenixcontact.com/us/products/0826255:M>

Technical data

Product properties

| | |
|--------------|------------------|
| Product type | Conductor marker |
|--------------|------------------|

Marking

| | |
|-----------|---------|
| Printing | M |
| Slot type | Profile |

Dimensions

| | |
|--------|---------|
| Width | 4.2 mm |
| Height | 9.5 mm |
| Length | 6.60 mm |

External dimensions

| | |
|------------------|----------------|
| Outside diameter | 4 mm ... 10 mm |
|------------------|----------------|

Material specifications

| | |
|--|--------------------------------|
| Color | yellow (RAL 1018) |
| Material | Polyvinyl chloride |
| Flammability rating according to UL 94 | V0 |
| Base element material | PVC |
| Components | Free from silicone and cadmium |

Cable/line

| | |
|-------------------------|----------------|
| External cable diameter | 4 mm ... 10 mm |
|-------------------------|----------------|

Environmental and real-life conditions

Ambient conditions

| | |
|---|---|
| Ambient temperature (operation) | -30 °C ... 60 °C |
| Recommended ambient temperature (storage/transport) | 23 °C |
| Recommended humidity (storage/transport) | 50 % (Storage in a dry and dark place in the original packaging is recommended) |

Test for substances that would hinder coating with paint or varnish

| | |
|---|-------------------------|
| Testing for paint wetting impairment substances (LABS-conformity) | VDMA 24364-A1-L:2018-05 |
| Result | Test passed |

Scratch resistance

| | |
|---------------|--------------------------------|
| Specification | EN ISO 1518-1:2023 (following) |
| Requirements | ≥ 5 N |
| Result | Test passed |

Tesafilm test

| | |
|---------------|-------------------------------------|
| Specification | DIN EN ISO 2409:2020-12 (following) |
|---------------|-------------------------------------|

SD-WMS 10 (CH)R YE:M - Wire marking tag



0826255:M

<https://www.phoenixcontact.com/us/products/0826255:M>

| | |
|--------|-------------|
| Result | Test passed |
|--------|-------------|

UV resistance

| | |
|---------------|---------------------------------------|
| Specification | DIN EN ISO 4892-2:2021-11 (following) |
| Result | Test passed |
| Test duration | 96 h |
| Procedure | Artificial irradiation. |

Temperature storage

| | |
|-------------------------|-----------------------|
| Specification | IEC 60068-2-2:2007-07 |
| Result | Test passed |
| Procedure | Test Bb |
| Duration | 96 h |
| Temperature for testing | 105 °C |

Temperature resistance

| | |
|-----------------------|---------------------------------|
| Specification | ANSI/UL 969-2018:03 (following) |
| Test duration | 240 h |
| Rating 80 °C (105 °C) | Test passed |

Wipe resistance of inscriptions

| | |
|---|--|
| Specification | DIN EN 61010-1 (VDE 0411-01):2020-03 DIN EN 62208 (VDE 0660-511):2012-06 (in parts) |
| Isopropanol (99%) [67-63-0] | Test passed |
| n-Hexane [CAS No. 110-54-3] | Test passed |
| Water + Petroleum ether [CAS No. 64742-82-1] | Test passed |
| Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2] | Test passed |
| Ethanol (99 %) [CAS No. 64-17-5] | Test passed |

Immersion in chemicals, oil & fuel

| | |
|---|--------------------------|
| Specification | ISO 175:2010 (following) |
| Test duration | 168 h |
| Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2] | Test passed |
| Saltwater (saturated 350 g/l) [CAS No. -] | Test passed |
| Ethanol (99 %) [CAS No. 64-17-5] | Test passed |
| Gasoline [CAS No. 64742-49-0] | Test passed |
| Diesel [CAS No. 68476-34-6] | Test passed |
| IRM 901 | Test passed |
| IRM 902 | Test passed |
| IRM 903 | Test passed |

SD-WMS 10 (CH)R YE:M - Wire marking tag



0826255:M

<https://www.phoenixcontact.com/us/products/0826255:M>

Testing in a condensation changing climate in the presence of sulfur dioxide

| | |
|---------------|--------------------------|
| Specification | DIN EN ISO 22479:2022-08 |
| Result | Test passed |
| Procedure | Method B |
| Cycles | 2 |

Salt spray test

| | |
|---------------|---|
| Specification | DIN EN IEC 60068-2-11 (VDE 0468-2-11):2022-10 |
| Result | Test passed |
| Test duration | 96 h |

Standards and regulations

| | |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|-----------------|-----------------------------|

Mounting

| | |
|---------------|-----------|
| Mounting type | thread on |
|---------------|-----------|

SD-WMS 10 (CH)R YE:M - Wire marking tag



0826255:M

<https://www.phoenixcontact.com/us/products/0826255:M>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27281102 |
| ECLASS-15.0 | 27281102 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC001530 |
|-----------|----------|

SD-WMS 10 (CH)R YE:M - Wire marking tag



0826255:M

<https://www.phoenixcontact.com/us/products/0826255:M>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com