

# SD-WMS 16 (NU):4 - Wire marking tag



0826394:4

<https://www.phoenixcontact.com/us/products/0826394:4>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Wire marking tag, labeled with the number: Numbers, white, mounting type: thread on

The figure shows the article SD-WMS 10 (CH)  
YE

## Commercial data

Item number	0826394:4
Packing unit	20 pc
Minimum order quantity	20 pc
Product key	BG222B
GTIN	4046356427227
Weight per piece (including packing)	0.743 g
Weight per piece (excluding packing)	0.743 g
Country of origin	SE

# SD-WMS 16 (NU):4 - Wire marking tag



0826394:4

<https://www.phoenixcontact.com/us/products/0826394:4>

## Technical data

### Product properties

Product type	Conductor marker
--------------	------------------

### Marking

Printing	Numbers
Slot type	Profile

### Dimensions

Width	6.2 mm
Height	16.5 mm
Length	11.00 mm

### External dimensions

Outside diameter	8 mm ... 16 mm
------------------	----------------

### Material specifications

Color	white
Material	Polyvinyl chloride
Flammability rating according to UL 94	V0

### Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

### Mounting

Mounting type	thread on
---------------	-----------

# SD-WMS 16 (NU):4 - Wire marking tag



0826394:4

<https://www.phoenixcontact.com/us/products/0826394:4>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)