

EMLP (22X22)R SR CUS - Label



0827475

<https://www.phoenixcontact.com/us/products/0827475>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Label, Roll, can be ordered: by line, labeled according to customer specifications, mounting type: adhesive, Number of individual labels: 2, text field height: 22 mm, text field width: 22 mm

Your advantages

- The EMLP ... self-adhesive markers are particularly suited to marking electrical components, devices, and buttons
- The markers meet the same standards as the engraved labels, they provide high-quality visuals
- When combined with the right ink ribbon, the marking is highly resistant to solvents and mechanical influences
- Labeling service: Phoenix Contact can custom-label all EMLP ... markers in accordance with your requirements

Commercial data

Item number	0827475
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	BG8141
GTIN	4046356433129
Weight per piece (including packing)	0.62 g
Weight per piece (excluding packing)	0.32 g
Country of origin	PL

Technical data

Product properties

Product type	Device marker
--------------	---------------

Marking

Number of individual labels	2
Number of individual labels per row	2
Identification technology	Thermotransfer

Dimensions

Width	21.80 mm
Height	21.80 mm
Depth	0.55 mm
Length	22 mm

Text field

Text field width	22 mm
Text field height	22 mm

Material specifications

RoHS compliant	yes
Foil strength	175 µm
Adhesive strength	400 µm
Adhesive	Acrylic
Color	silver-colored
Material	Polyester
Base element material	Polyester
Components	Silicone-free

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 120 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)

Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VDMA 24364-A1-L:2018-05
Result	Test passed

Scratch resistance

Specification	DIN EN ISO 1518-1:2019-10 (following)
Requirements	≥ 5 N

EMLP (22X22)R SR CUS - Label



0827475

<https://www.phoenixcontact.com/us/products/0827475>

Result	Test passed
--------	-------------

Tesafilem test

Specification	DIN EN ISO 2409:2013 (following)
Result	Test passed

UV resistance

Specification	ISO 4892-2:2013-03 (following)
Result	Test passed
Test duration	96 h
Procedure	Artificial irradiation.

Temperature resistance

Specification	ANSI/UL 969-2018:03 (following)
Test duration	240 h
Rating 150 °C (180 °C)	Test passed

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03 DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropanol (99%) [67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed
Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2]	Test passed
Ethanol (99 %) [CAS No. 64-17-5]	Test passed

Immersion in chemicals, oil & fuel

Specification	ISO 175:2010 (following)
Test duration	168 h
Saltwater (saturated 350 g/l) [CAS No. -]	Test passed
Diesel [CAS No. 68476-34-6]	Test passed
IRM 901	Test passed
IRM 902	Test passed
IRM 903	Test passed

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	EN ISO 22479:2022-06
Result	Test passed
Cycles	2

Salt spray test

Specification	DIN EN IEC 60068-2-11 (VDE 0468-2-11):2022-10
Result	Test passed

EMLP (22X22)R SR CUS - Label



0827475

<https://www.phoenixcontact.com/us/products/0827475>

Test duration	96 h
---------------	------

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Mounting

Mounting type	adhesive
---------------	----------

EMLP (22X22)R SR CUS - Label



0827475

<https://www.phoenixcontact.com/us/products/0827475>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/0827475>



cULus Recognized

Approval ID: MH48542-20251115

EMLP (22X22)R SR CUS - Label



0827475

<https://www.phoenixcontact.com/us/products/0827475>

Classifications

ECLASS

ECLASS-13.0	27281103
ECLASS-15.0	27281103

ETIM

ETIM 10.0	EC001288
-----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

EMLP (22X22)R SR CUS - Label



0827475

<https://www.phoenixcontact.com/us/products/0827475>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com