

# UC-WMT (10X4) VT CUS - Cable marker



0826789

<https://www.phoenixcontact.com/us/products/0826789>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Cable marker, can be ordered: by sheet, violet (RAL 4005), labeled according to customer specifications, cable diameter range: 0.6 ... 7 mm, mounting type: insert, Number of individual labels: 48



## Your advantages

- The UC-WMT ... UniCard labeling range includes markers for conductor marking with marking collars from the PATG (HF) .../PATG ... system
- To simplify mounting, the insert labels are arranged on UniCard sheets so that they can be separated branch by branch
- Labeled insert strips are simply inserted into the collars. This protects the marking against dirt.
- The sheets provide space for including function texts
- The format automatically ensures printing with a high degree of positioning accuracy
- Marking service: Phoenix Contact can custom-mark all UniCard markers according to your specifications

## Commercial data

Item number	0826789
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	BG8127
GTIN	4046356363983
Weight per piece (including packing)	11.58 g
Weight per piece (excluding packing)	8.7 g
Country of origin	PL

# UC-WMT (10X4) VT CUS - Cable marker



0826789

<https://www.phoenixcontact.com/us/products/0826789>

## Technical data

### Product properties

Product type	Conductor marker
--------------	------------------

### Marking

Number of individual labels	48
Number of individual labels per row	8
Slot type	Card form
Identification technology	UV LED technology

### Dimensions

Width	10 mm
Length	4 mm

### Material specifications

RoHS compliant	yes
Color	violet (RAL 4005)
Material	PA
Flammability rating according to UL 94	V2
Base element material	PA
Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21))	120 °C
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 2
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 2
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 2
Components	free from silicone and halogen

### Cable/line

External cable diameter	0.6 mm ... 7 mm
-------------------------	-----------------

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 120 °C
---------------------------------	-------------------

#### Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VW PV 3.10.7:2005-02
Result	Test passed

#### UV resistance

Specification	ISO 4892-2:2013-03 (following)
Result	Test passed
Test duration	96 h

# UC-WMT (10X4) VT CUS - Cable marker



0826789

<https://www.phoenixcontact.com/us/products/0826789>

## Standards and regulations

Wipe resistance

DIN EN 61010-1 (VDE 0411-1)

## Mounting

Mounting type

insert

# UC-WMT (10X4) VT CUS - Cable marker



0826789

<https://www.phoenixcontact.com/us/products/0826789>

## Classifications

### UNSPSC

UNSPSC 21.0	39131700
-------------	----------

# UC-WMT (10X4) VT CUS - Cable marker



0826789

<https://www.phoenixcontact.com/us/products/0826789>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)