

SK CUS - Marker card



0828492

<https://www.phoenixcontact.com/us/products/0828492>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Marker card, can be ordered: by card, white (RAL 9010), labeled according to customer specifications, mounting type: adhesive

Your advantages

- The SK labeling range offers self-adhesive marker strips for labeling products that do not have a marker groove
- The markers that are supplied in roll format can be labeled quickly and cost-effectively using THERMOMARK printers
- Labeling service: Phoenix Contact can custom-label all SK ... markers in accordance with your requirements

Commercial data

Item number	0828492
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	BG8113
GTIN	4046356512633
Weight per piece (including packing)	0.9 g
Weight per piece (excluding packing)	0.9 g
Country of origin	PL

Technical data

Notes

Order information:	Marking up to max. 25-pos.
--------------------	----------------------------

Product properties

Product type	Terminal marker
--------------	-----------------

Marking

Slot type	Label
-----------	-------

Dimensions

Width	50 mm
-------	-------

Material specifications

Foil strength	53 µm
Adhesive strength	20 µm
Adhesive	Acrylic
Color	white (RAL 9010)
Material	Polyester
Base element material	Polyester
Components	free from silicone and halogen

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 150 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)

Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VW PV 3.10.7:2005-02
Result	Test passed

UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
Result	Test passed
Test duration	96 h

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

SK CUS - Marker card

0828492

<https://www.phoenixcontact.com/us/products/0828492>



Mounting

Mounting type

adhesive

SK CUS - Marker card

0828492

<https://www.phoenixcontact.com/us/products/0828492>



Drawings

Schematic diagram



- ① Horizontal
- ② Vertical

SK CUS - Marker card



0828492

<https://www.phoenixcontact.com/us/products/0828492>

Classifications

ECLASS

ECLASS-13.0	27281101
ECLASS-15.0	27281101

ETIM

ETIM 10.0	EC000761
-----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

SK CUS - Marker card



0828492

<https://www.phoenixcontact.com/us/products/0828492>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com