

KMV 44X9,6 CUS - Stainless steel label



0828494

<https://www.phoenixcontact.com/us/products/0828494>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Stainless steel label, Stainless steel label, can be ordered: Piece, labeled according to customer specifications, cable diameter range: 1 ... 63 mm, mounting type: Assembly with cable ties, Number of individual labels: 1, text field height: 9 mm, text field width: 23 mm

Your advantages

- Easy assembly with UNIFOX-CT M7,9
- Secured using stainless steel cable binders
- Cable markers for marking cables and conductors with larger cross sections
- The individual stainless steel markers are pushed onto the corresponding holders

Commercial data

Item number	0828494
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	BG8145
GTIN	4046356512657
Weight per piece (including packing)	0.7 g
Weight per piece (excluding packing)	0.7 g
Country of origin	PL

KMV 44X9,6 CUS - Stainless steel label



0828494

<https://www.phoenixcontact.com/us/products/0828494>

Technical data

Product properties

Product type	Conductor marker
--------------	------------------

Marking

Number of individual labels	1
Slot type	Mounting set

Dimensions

Width	9.60 mm
Height	44.00 mm
Depth	1.00 mm
Length	44 mm

Text field

Text field width	23 mm
Text field height	9 mm

Material specifications

Color	silver-colored
Material	Stainless steel 304
Base element material	Stainless steel

Cable/line

External cable diameter	1 mm ... 63 mm
-------------------------	----------------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-80 °C ... 538 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)

UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
---------------	---------------------------------------

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)

Mounting

Mounting type	Assembly with cable ties
---------------	--------------------------

KMV 44X9,6 CUS - Stainless steel label



0828494

<https://www.phoenixcontact.com/us/products/0828494>

Classifications

ECLASS

ECLASS-13.0	27281102
ECLASS-15.0	27281102

ETIM

ETIM 10.0	EC001530
-----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

KMV 44X9,6 CUS - Stainless steel label



0828494

<https://www.phoenixcontact.com/us/products/0828494>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com