

# EML (44X49)R-ME - Label for ME ... F-UT ... TBUS ... housing



0828169

<https://www.phoenixcontact.com/us/products/0828169>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Label for ME ... F-UT ... TBUS ... housing, Roll, white (RAL 9010), unmarked, can be labeled with: THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, THERMOMARK ROLL X1, THERMOMARK ROLL 2.0, THERMOMARK ROLL, mounting type: adhesive, Number of individual labels: 200, text field height: 49 mm, text field width: 44 mm

## Your advantages

- The EML ... self-adhesive device markers are particularly suitable for identification of various types of equipment in controller, system, and control cabinet building
- When combined with the right ink ribbon, the marking is highly resistant to solvents and mechanical influences
- The EML ... materials are UL-listed
- Labeling service: Phoenix Contact can custom-label all EM ... markers in accordance with your requirements
- A wide range of marker sizes and colors are available for custom designs

## Commercial data

Item number	0828169
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BG16
Product key	BG2411
GTIN	4046356484091
Weight per piece (including packing)	138 g
Weight per piece (excluding packing)	99.99 g
Customs tariff number	39269097
Country of origin	PL

# EML (44X49)R-ME - Label for ME ... F-UT ... TBUS ... housing



0828169

<https://www.phoenixcontact.com/us/products/0828169>

## Technical data

### Product properties

Product type	Device marker
--------------	---------------

### Marking

Number of individual labels	200
Number of individual labels per row	1
Identification technology	Thermotransfer

### Dimensions

Width	44.30 mm
Height	49.40 mm
Depth	0.08 mm

### Text field

Text field width	44 mm
Text field height	49 mm

### Material specifications

Color	white (RAL 9010)
Material	Polyester
Base element material	Polyester
Components	free from silicone and halogen

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 150 °C
Recommended ambient temperature (storage/transport)	21 °C
Recommended humidity (storage/transport)	50 %

#### UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
Result	Test passed
Test duration	96 h
Procedure	Artificial irradiation.

#### Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-1):2011-07 DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropanol (99%) [67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed

# EML (44X49)R-ME - Label for ME ... F-UT ... TBUS ... housing



0828169

<https://www.phoenixcontact.com/us/products/0828169>

## Standards and regulations

Wipe resistance

DIN EN 61010-1 (VDE 0411-1)

## Mounting

Mounting type

adhesive

# EML (44X49)R-ME - Label for ME ... F-UT ... TBUS ... housing



0828169

<https://www.phoenixcontact.com/us/products/0828169>

## Classifications

### ECLASS

ECLASS-13.0	27281103
ECLASS-15.0	27281103

### ETIM

ETIM 10.0	EC001288
-----------	----------

### UNSPSC

UNSPSC 21.0	39131500
-------------	----------

# EML (44X49)R-ME - Label for ME ... F-UT ... TBUS ... housing



0828169

<https://www.phoenixcontact.com/us/products/0828169>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)