

SK 3,8 REEL P9,5 WH CUS - Marker card



0828496

<https://www.phoenixcontact.com/us/products/0828496>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Marker card, Roll, can be ordered: by card, white (RAL 9010), labeled according to customer specifications, mounting type: adhesive, for terminal block width: 9.5 mm, Number of individual labels: 12

Your advantages

- The markers that are supplied in roll format can be labeled quickly and cost-effectively using THERMOMARK printers
- The SK labeling range offers self-adhesive marker strips for labeling products that do not have a marker groove
- Labeling service: Phoenix Contact can custom-label all SK ... markers in accordance with your requirements

Commercial data

Item number	0828496
Packing unit	1 pc
Minimum order quantity	50 pc
Note	Made to order (non-returnable)
Sales key	BG24
Product key	BG8113
GTIN	4046356512671
Weight per piece (including packing)	1.79 g
Weight per piece (excluding packing)	1.06 g
Customs tariff number	49119900
Country of origin	DE

SK 3,8 REEL P9,5 WH CUS - Marker card



0828496

<https://www.phoenixcontact.com/us/products/0828496>

Technical data

Notes

Order information:	Marking up to max. 25-pos.
--------------------	----------------------------

Product properties

Product type	Terminal marker
Pitch	9.5 mm

Marking

Number of individual labels	12
Number of individual labels per row	1
Number of marker strips	12
Slot type	Label
Identification technology	Thermal transfer

Dimensions

Width	50.00 mm
Height	3.80 mm
Depth	0.07 mm
Pitch	9.5 mm

Material specifications

Foil strength	53 µm
Adhesive strength	20 µm
Adhesive	Acrylic
Color	white (RAL 9010)
Material	Polyester
Base element material	Polyester
Components	free from silicone and halogen

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 150 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)

Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VW PV 3.10.7:2005-02
Result	Test passed

UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
---------------	---------------------------------------

SK 3,8 REEL P9,5 WH CUS - Marker card



0828496

<https://www.phoenixcontact.com/us/products/0828496>

Result	Test passed
Test duration	96 h

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Mounting

Mounting type	adhesive
---------------	----------

SK 3,8 REEL P9,5 WH CUS - Marker card

0828496

<https://www.phoenixcontact.com/us/products/0828496>

Drawings

Schematic diagram



- ① Horizontal
- ② Vertical

SK 3,8 REEL P9,5 WH CUS - Marker card



0828496

<https://www.phoenixcontact.com/us/products/0828496>

Classifications

ECLASS

ECLASS-13.0	27281101
ECLASS-15.0	27281101

ETIM

ETIM 10.0	EC000761
-----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

SK 3,8 REEL P9,5 WH CUS - Marker card



0828496

<https://www.phoenixcontact.com/us/products/0828496>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com