

US-EMP (60X15) SR - Snap-in markers



0828857

<https://www.phoenixcontact.com/us/products/0828857>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Snap-in markers, Card, unmarked, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, THERMOMARK PRIME 2.0, mounting type: insert, Number of individual labels: 9, text field height: 15 mm, text field width: 60 mm



Your advantages

- The markers, which are supplied in uniform sheets, can be labeled quickly, easily, and cost-effectively using the THERMOMARK CARD
- The perforated markers and labels are easy to separate and can be easily fitted
- The sheets provide space for including function texts
- The US-EMP ... UniSheet labeling range includes markers that can be fitted into existing CARRIER EMP ... label frames

Commercial data

Item number	0828857
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BG09
Product key	BG2419
GTIN	4046356558648
Weight per piece (including packing)	14.7 g
Weight per piece (excluding packing)	14.7 g
Customs tariff number	39269097
Country of origin	DE

US-EMP (60X15) SR - Snap-in markers



0828857

<https://www.phoenixcontact.com/us/products/0828857>

Technical data

Product properties

Product type	Device marker
--------------	---------------

Marking

Number of individual labels	9
Number of individual labels per row	1
Identification technology	Thermotransfer

Dimensions

Width	59.70 mm
Height	14.90 mm
Depth	0.50 mm
Length	14.9 mm

Text field

Text field width	60 mm
Text field height	15 mm

Material specifications

RoHS compliant	yes
Foil strength	500 µm
Color	silver-colored
Material	PVC PVC
Flammability rating according to UL 94	V0
Components	Silicone-free

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-30 °C ... 80 °C
Recommended ambient temperature (storage/transport)	10 °C
Recommended humidity (storage/transport)	35 % ... 65 %

Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VW PV 3.10.7:2005-02
Result	Test passed

UV resistance

Specification	ISO 4892-2:2013-03 (following)
Result	Test passed
Test duration	96 h

Wipe resistance of inscriptions

US-EMP (60X15) SR - Snap-in markers



0828857

<https://www.phoenixcontact.com/us/products/0828857>

Specification	IEC 61010-1:2010-06
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropanol (99%) [67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	DIN 50018:2013-05 (following)
Result	Test passed
Climate level	AHT 1.0 S
Cycles	2

Salt spray test

Specification	DIN EN 60068-2-11:2000-02
Result	Test passed

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Mounting

Mounting type	insert
---------------	--------

US-EMP (60X15) SR - Snap-in markers



0828857

<https://www.phoenixcontact.com/us/products/0828857>

Classifications

ECLASS

ECLASS-13.0

27281106

ETIM

ETIM 9.0

EC001530

UNSPSC

UNSPSC 21.0

39131700

US-EMP (60X15) SR - Snap-in markers



0828857

<https://www.phoenixcontact.com/us/products/0828857>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
-----------------------------------------	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com