

ZBF 13 CUS - Zack Marker strip, flat

0829134

<https://www.phoenixcontact.com/us/products/0829134>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Zack Marker strip, flat, can be ordered: Strip, white (RAL 9010), labeled according to customer specifications, mounting type: snap into flat marker groove, for terminal block width: 13 mm, Number of individual labels: 5, text field height: 5.2 mm, text field width: 13 mm

Your advantages

- The ZBF zack marker strip system with flat marker groove is a marking solution for modular terminal blocks and electronics modules
- Other pitches available on request
- Labeling service: Phoenix Contact can custom-label all zack marker strip markers according to your requirements
- The multi-section marking strips are easy to fit and can be easily separated if required

Commercial data

Item number	0829134
Packing unit	1 pc
Minimum order quantity	50 pc
Note	Made to order (non-returnable)
Sales key	BG24
Product key	BG8112
GTIN	4046356546706
Weight per piece (including packing)	0.612 g
Weight per piece (excluding packing)	0.411 g
Customs tariff number	49119900
Country of origin	DE

ZBF 13 CUS - Zack Marker strip, flat



0829134

<https://www.phoenixcontact.com/us/products/0829134>

Technical data

Product properties

Product type	Terminal marker
Pitch	13 mm

Marking

Number of individual labels	5
Number of individual labels per row	5
Number of marker strips	1
Slot type	flat

Dimensions

Width	13.00 mm
Height	6.40 mm
Depth	1.60 mm
Pitch	13 mm
Length	6.4 mm

Text field

Text field width	13 mm
Text field height	5.2 mm

Material specifications

Color	white (RAL 9010)
Material	PA PA
Flammability rating according to UL 94	V2
Base element material	PA
Components	free from silicone and halogen

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)

UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
---------------	---------------------------------------

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03 DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
---------------	--

ZBF 13 CUS - Zack Marker strip, flat



0829134

<https://www.phoenixcontact.com/us/products/0829134>

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
	DIN EN 61010-1 (VDE 0411-1)
	DIN VDE 0611
	DIN VDE 0611

Mounting

Mounting type	snap into flat marker groove
---------------	------------------------------

ZBF 13 CUS - Zack Marker strip, flat

0829134

<https://www.phoenixcontact.com/us/products/0829134>



Drawings

Schematic diagram



- ① Horizontal
- ② Vertical

ZBF 13 CUS - Zack Marker strip, flat



0829134

<https://www.phoenixcontact.com/us/products/0829134>

Classifications

ECLASS

ECLASS-13.0	27281101
ECLASS-15.0	27281101

ETIM

ETIM 10.0	EC000761
-----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

ZBF 13 CUS - Zack Marker strip, flat



0829134

<https://www.phoenixcontact.com/us/products/0829134>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com