

US2-TM 100 - Marker for terminal blocks



0829268

<https://www.phoenixcontact.com/us/products/0829268>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

UniSheet labels for terminal blocks from Wago, can be labeled with THERMOMARK CARD, 12-section, color: white



Your advantages

- The cards provide space for including function texts
- The US2-TM 100 UniSheet markers are suitable for Wago terminal blocks
- The perforated marking strips are easy to separate and can be easily fitted
- Labeling service: Phoenix Contact can custom-label all UniSheet markers according to your requirements
- The markers, which are supplied as uniform cards, can be labeled quickly, easily, and cost-effectively using the THERMOMARK CARD

Commercial data

Item number	0829268
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BG09
Product key	BG2119
GTIN	4046356559591
Weight per piece (including packing)	10.04 g
Weight per piece (excluding packing)	10.08 g
Customs tariff number	39204910
Country of origin	DE

US2-TM 100 - Marker for terminal blocks



0829268

<https://www.phoenixcontact.com/us/products/0829268>

Technical data

Product properties

Product type	Terminal marker
Area of application	Wago: Terminal blocks
Pitch	104 mm

Marking

Number of individual labels	12
Number of individual labels per row	1
Slot type	flat
Identification technology	Thermotransfer, UV-LED-Technologie

Dimensions

Width	104.00 mm
Height	10.90 mm
Depth	0.30 mm
Pitch	104 mm

Text field

Text field width	104 mm
Text field height	10.9 mm

Material specifications

Color	white (RAL 9010)
Material	PVC
Flammability rating according to UL 94	V0
Base element material	PVC
Components	Silicone-free

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-30 °C ... 80 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)

Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VW PV 3.10.7:2005-02
Result	Test passed

UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
Result	Test passed

US2-TM 100 - Marker for terminal blocks



0829268

<https://www.phoenixcontact.com/us/products/0829268>

Test duration	96 h
---------------	------

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-1):2011-07 DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropanol (99%) [67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	DIN EN ISO 22479:2022-08
Result	Test passed
Procedure	Method B
Cycles	2

Salt spray test

Specification	DIN EN IEC 60068-2-11 (VDE 0468-2-11):2022-10
Result	Test passed

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Mounting

Mounting type	latching
---------------	----------

US2-TM 100 - Marker for terminal blocks



0829268

<https://www.phoenixcontact.com/us/products/0829268>

Classifications

ECLASS

ECLASS-13.0	27281101
ECLASS-15.0	27281101

ETIM

ETIM 10.0	EC000761
-----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

US2-TM 100 - Marker for terminal blocks



0829268

<https://www.phoenixcontact.com/us/products/0829268>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com