

ZB 3,5 CUS - Zack marker strip



0829415

<https://www.phoenixcontact.com/us/products/0829415>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Zack marker strip, can be ordered: Strip, white (RAL 9010), labeled according to customer specifications, mounting type: latching, for terminal block width: 3.5 mm, Number of individual labels: 10, text field height: 10.5 mm, text field width: 3.5 mm

Your advantages

- Other pitches available on request
- The multi-section marking strips are easy to fit and can be easily separated if required
- Labeling service: Phoenix Contact can custom-label all zack marker strip markers according to your requirements
- The ZB zack marker strip system is a marking solution for modular terminal blocks and electronics modules with tall marker grooves
- Unmarked marking strips can be custom-labeled with a plotter or by hand

Commercial data

Item number	0829415
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	BG8112
GTIN	4046356554169
Weight per piece (including packing)	0.99 g
Weight per piece (excluding packing)	0.96 g
Country of origin	PL

ZB 3,5 CUS - Zack marker strip



0829415

<https://www.phoenixcontact.com/us/products/0829415>

Technical data

Notes

General	labeled according to customer specifications
General	labeled according to customer specifications

Product properties

Product type	Terminal marker
Pitch	3.5 mm

Marking

Number of individual labels	10
Number of individual labels per row	10
Number of marker strips	10
Slot type	high

Dimensions

Width	3.50 mm
Height	10.50 mm
Depth	4.20 mm
Pitch	3.5 mm
Length	10.5 mm

Text field

Text field width	3.5 mm
Text field height	10.5 mm

Material specifications

Color	white (RAL 9010)
Material	PA
Flammability rating according to UL 94	V2
Base element material	PA
Components	free from silicone and halogen

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)

UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
---------------	---------------------------------------

Wipe resistance of inscriptions

ZB 3,5 CUS - Zack marker strip



0829415

<https://www.phoenixcontact.com/us/products/0829415>

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Mounting

Mounting type	latching
---------------	----------

ZB 3,5 CUS - Zack marker strip


0829415

<https://www.phoenixcontact.com/us/products/0829415>



Drawings

Schematic diagram



- ① Horizontal
- ② Vertical

ZB 3,5 CUS - Zack marker strip



0829415

<https://www.phoenixcontact.com/us/products/0829415>

Classifications

ECLASS

ECLASS-13.0	27281101
ECLASS-15.0	27281101

ETIM

ETIM 10.0	EC000761
-----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

ZB 3,5 CUS - Zack marker strip



0829415
<https://www.phoenixcontact.com/us/products/0829415>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com