


ZB 17 CUS - Zack marker strip



0829393

<https://www.phoenixcontact.com/us/products/0829393>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Zack marker strip, can be ordered: Strip, white (RAL 9010), labeled according to customer specifications, mounting type: latching, for terminal block width: 17 mm, Number of individual labels: 50, text field height: 10.5 mm, text field width: 17 mm

Your advantages

- Labeling service: Phoenix Contact can custom-label all zack marker strip markers according to your requirements
- The ZB zack marker strip system is a marking solution for modular terminal blocks and electronics modules with tall marker grooves

Commercial data

Item number	0829393
Packing unit	1 pc
Minimum order quantity	10 pc
Note	Made to order (non-returnable)
Sales key	BG24
Product key	BG8112
GTIN	4046356547475
Weight per piece (including packing)	3 g
Weight per piece (excluding packing)	1.98 g
Customs tariff number	49119900
Country of origin	DE

ZB 17 CUS - Zack marker strip



0829393

<https://www.phoenixcontact.com/us/products/0829393>

Technical data

Notes

General	labeled according to customer specifications
General	labeled according to customer specifications

Product properties

Product type	Terminal marker
Pitch	17 mm

Marking

Number of individual labels	50
Number of individual labels per row	5
Number of marker strips	10
Slot type	high

Dimensions

Width	17.00 mm
Height	10.50 mm
Depth	4.20 mm
Pitch	17 mm
Length	10.5 mm

Text field

Text field width	17 mm
Text field height	10.5 mm

Material specifications

Color	white (RAL 9010)
Material	PA
	PA
Flammability rating according to UL 94	V2
Base element material	PA
Components	free from silicone and halogen

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)

UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
---------------	---------------------------------------

ZB 17 CUS - Zack marker strip

0829393

<https://www.phoenixcontact.com/us/products/0829393>



Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
	DIN EN 61010-1 (VDE 0411-1)
	DIN VDE 0611
	DIN VDE 0611

Mounting

Mounting type	latching
---------------	----------

ZB 17 CUS - Zack marker strip


0829393

<https://www.phoenixcontact.com/us/products/0829393>



Drawings

Schematic diagram



- ① Horizontal
- ② Vertical

ZB 17 CUS - Zack marker strip

0829393

<https://www.phoenixcontact.com/us/products/0829393>



Classifications

ECLASS

ECLASS-13.0	27281101
ECLASS-15.0	27281101

ETIM

ETIM 10.0	EC000761
-----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

ZB 17 CUS - Zack marker strip



0829393

<https://www.phoenixcontact.com/us/products/0829393>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com