

# CARRIER/L-EMP (1000X15) TR - Marker carriers



0829560

<https://www.phoenixcontact.com/us/products/0829560>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Profile, self-adhesive, 1000 mm long, for accommodating UC-,/US-, LS-, and EMT (EX15)R material, 15 mm height

## Commercial data

Item number	0829560
Packing unit	25 pc
Minimum order quantity	25 pc
Sales key	BG12
Product key	BG241A
GTIN	4046356614917
Weight per piece (including packing)	27.5 g
Weight per piece (excluding packing)	27.5 g
Customs tariff number	39162000
Country of origin	DE

# CARRIER/L-EMP (1000X15) TR - Marker carriers



0829560

<https://www.phoenixcontact.com/us/products/0829560>

## Technical data

### Product properties

Product type	Marker carriers
--------------	-----------------

### Dimensions

Width	1000 mm
Height	17.6 mm
Depth	6.6 mm

### Text field

Text field width	1000 mm
Text field height	15 mm

### Material specifications

RoHS compliant	yes
Adhesive	Acrylic
Color	transparent
Material	PVC
Base element material	PVC
Components	Silicone-free

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 60 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %

#### Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VW PV 3.10.7:2005-02
Result	Test passed

#### UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
Result	Test passed
Test duration	96 h
Procedure	Artificial irradiation.

#### Temperature storage

Specification	IEC 60068-2-2:2007-07
Result	Test passed
Procedure	Test Bb
Duration	96 h
Maximum temperature	+60 °C

# CARRIER/L-EMP (1000X15) TR - Marker carriers



0829560

<https://www.phoenixcontact.com/us/products/0829560>

## Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	DIN EN ISO 22479:2022-08
Result	Test passed
Procedure	Method B
Cycles	2

## Salt spray test

Specification	DIN EN IEC 60068-2-11 (VDE 0468-2-11):2022-10
Result	Test passed

## Mounting

Mounting type	adhesive
---------------	----------

# CARRIER/L-EMP (1000X15) TR - Marker carriers



0829560

<https://www.phoenixcontact.com/us/products/0829560>

## Classifications

### ECLASS

ECLASS-13.0	27281105
ECLASS-15.0	27281105

### ETIM

ETIM 10.0	EC002248
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# CARRIER/L-EMP (1000X15) TR - Marker carriers



0829560

<https://www.phoenixcontact.com/us/products/0829560>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

### EF3.1 Climate Change

CO2e kg	0.495 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)