ZBF 10/5,8 AXL UNPRINTED - Zack Marker strip, flat

0829580

https://www.phoenixcontact.com/us/products/0829580

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Zack Marker strip, flat, Strip, white (RAL 9010), unmarked, can be labeled with: PLOTMARK, CMS-P1-PLOTTER, mounting type: latching, for terminal block width: 10.15 mm, Number of individual labels: 50, text field height: 5 mm, text field width: 10.15 mm

Commercial data

Item number	0829580
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	NULL
Product key	BG2112
GTIN	4046356591256
Weight per piece (including packing)	0.327 g
Weight per piece (excluding packing)	0.28 g
Customs tariff number	39269097
Country of origin	DE

Technical data

Product properties

Product type	Terminal marker
Pitch	10.15 mm

Marking

Number of individual labels	50
Number of individual labels per row	5
Number of marker strips	5
Marking groove	flat

Dimensions

Width	46.40 mm
Height	6.40 mm
Depth	1.60 mm
Pitch	10.15 mm

Text field

Text field width	10.15 mm
Text field height	5 mm

Material specifications

Color	white (RAL 9010)
Material	PA
Flammability rating according to UL 94	V2
Base element material	PA
Components	free from silicone and halogen

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)

UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)

Mounting

Mounting type	latching

Classifications

ECLASS

ECLASS-13.0	27281101
ECLASS-15.0	27281101

ETIM

ETIM 10.0	EC000761

UNSPSC

UNSPSC 21.0	39131500

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

EF3.1 Climate Change

CO2e kg	0.004 kg CO2e

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com