

# US-WMT (18X4) CUS - Cable marker



0829978

<https://www.phoenixcontact.com/us/products/0829978>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Cable marker, Card, can be ordered: by card, white (RAL 9010), labeled according to customer specifications, cable diameter range: 0.6 ... 22 mm, mounting type: insert, Number of individual labels: 70, text field height: 4 mm, text field width: 18 mm



## Your advantages

- The US-WMT ... UniSheet labeling range includes markers for conductor marking with marking collars from the PATG/PATO ... system
- Labeling service: Phoenix Contact can custom-label all UniSheet markers according to your requirements

## Commercial data

Item number	0829978
Packing unit	1 pc
Minimum order quantity	10 pc
Note	Made to order (non-returnable)
Sales key	BG24
Product key	BG8129
GTIN	4046356613026
Weight per piece (including packing)	16.1 g
Weight per piece (excluding packing)	16.1 g
Customs tariff number	49119900
Country of origin	DE

# US-WMT (18X4) CUS - Cable marker



0829978

<https://www.phoenixcontact.com/us/products/0829978>

## Technical data

### Product properties

Product type	Conductor marker
--------------	------------------

### Marking

Number of individual labels	70
Number of individual labels per row	14
Identification technology	Thermotransfer

### Dimensions

Width	4.5 mm
Length	18 mm

### Text field

Text field width	18 mm
Text field height	4 mm

### Material specifications

Color	white (RAL 9010)
Material	PVC
Flammability rating according to UL 94	V0
Base element material	PVC
Components	Silicone-free

### Cable/line

External cable diameter	0.6 mm ... 22 mm
-------------------------	------------------

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-30 °C ... 80 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)

#### Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VW PV 3.10.7:2005-02
Result	Test passed

#### UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
Result	Test passed
Test duration	96 h

#### Wipe resistance of inscriptions

# US-WMT (18X4) CUS - Cable marker



0829978

<https://www.phoenixcontact.com/us/products/0829978>

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)

## Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

## Mounting

Mounting type	insert
---------------	--------

# US-WMT (18X4) CUS - Cable marker



0829978

<https://www.phoenixcontact.com/us/products/0829978>

## Classifications

### ECLASS

ECLASS-13.0	27281106
ECLASS-15.0	27281106

### ETIM

ETIM 10.0	EC001288
-----------	----------

### UNSPSC

UNSPSC 21.0	39131700
-------------	----------

# US-WMT (18X4) CUS - Cable marker



0829978

<https://www.phoenixcontact.com/us/products/0829978>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

### EF3.1 Climate Change

CO2e kg	0.017 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)